





RoHS Compliant

Rev.		Sign	Date	Description	Approver
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!					

Technical Specification:

- Current: 80A.
- Torque: 15 lbf.in.
- Mark" " is the Critical dimension.



ITEM	PART NAME	DESCRIPTION	Q'ty
①	Spacer	Steel, Matte Tin Plated	1PCS
②	terminal	Copper alloy, Matte Tin Plated	1PCS

Amphenol
ANYTEK

CUSTOMER COPY
ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		AMT45028DB Stamped terminal						
PART NO.		AMT0450028DB0000G			DWG NO.		8AMT0025	
APPROVED		CHECKED	DESIGNED	DRAWN	CUST NO.		Tolerance	
		Seamus 2023.10.23	Seamus 2023.10.23					
				SHEET: 01/01		UNIT: mm		
				SCALE: NONE		REV: A0		
						ANGLES ±1°		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[AMT0450028DB0000G](#)