





RoHS Compliant

Rev./SIGN		DATE	DESCRIPTION	APPROVER
THIS IS CAD DRAWING. DO NOT REVISE MANUALLY!!!				

Technical Specification:

- Current: 115A.
- Torque: 20 lbf.in.
- Mark "▲" is the Critical dimension.



①	Spacer	Steel , Matte Tin Plated	1PCS
②	terminal	Copper alloy, Matte Tin Plated	1PCS
ITEM	PART NAME	DESCRIPTION	Q'ty

TITLE		AMT66007DB Stamped terminal		DWG NO.		8AMT0034		Tolerance	
PART NO.		AMT0660007DB0000G		DRAWN		Seamus		UNIT: mm	
APPROVED		CHECKED		DESIGNED		2023.10.23		SCALE: NONE	
								REVISIONS	
								SHEET: 01/01	
								ANGLES: ±1°	

Amphenol
ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

PCB LAYOUT

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[AMT0660007DB0000G](#)