


NOTES: UNLESS OTHERWISE SPECIFIED

1. MATERIAL: THERMOPLASTIC, HOUSING COLOR: GREY
INSERT COLOR: PER KEY CONFIGURATION
2. RoHS COMPLIANT
3. MOISTURE RESISTANCE: IP68 (1M OF WATER FOR
A PERIOD OF 24 HOURS , MATED CONDITION)
4. TEMPERATURE RANGE: -55C~125C
5. USE WITH CONNECTORS ATM06-08SX*
(X = A,B,C,D KEYS; * = MODIFICATIONS AND/OR COLORS)
6. ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.

KEYWAY (3) PLACES TYP
KEY-A CONFIGURATION
P/N ATM06-08SA-CAP
INSERT COLOR: GRAY



KEY-B CONFIGURATION
P/N ATM06-08SB-CAP
INSERT COLOR: BLACK

KEY-C CONFIGURATION
P/N ATM06-08SC-CAP
INSERT COLOR: GREEN

KEY-D CONFIGURATION
P/N ATM06-08SD-CAP
INSERT COLOR: BROWN

REVISIONS					
REV	ECO	DESCRIPTION	DATE	BY	APPROVED
A1	-	RELEASE	26JUN15	JA	
A2	-	REVISED COLOR AND IP RATING	20NOV2020	JA	DH

	SEE KEY OPTIONS		
	PART NUMBER	DESCRIPTION	ITEM
QUANTITY	MATERIALS LIST		
UNLESS OTHERWISE SPECIFIED		SIGNATURES	DATE
1) All dimensions are in metric(mm).		DRAWN: J. HEAD	23JUN2015
2) Tolerances are as follows:		CHECKED:	
1 PL DEC ±0.30 Fractions 1st/64		ENGINEER:	
2 PL DEC ±0.15 Angles ±1		APPROVAL:	
3) Note reference = 			
MATERIAL SPECIFICATIONS:		CUSTOMER:	
PROCESS SPECIFICATIONS:		THIS DRAWING IS SUPPLIED FOR INFORMATION ONLY. DESIGN FEATURES, SPECIFICATIONS AND PERFORMANCE DATA SHOWN HEREON ARE THE PROPERTY OF THE AMPHENOL CORPORATION. NO RIGHTS OF REPRODUCTION ARE IMPLIED. ALL DIMENSIONS ARE SUBJECT TO NORMAL MANUFACTURING VARIATIONS.	
NEXT ASSY:	SIZE	TYPE	DWG NO.
	B	C-	ATM06-08SX-CAP
	SCALE	NONE	REVISION
			A2
		SHEET	1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[ATM06-08SC-CAP](#)