




REV.	ECN NO.	DATE	SIGN	DESCRIPTION
C	LEN-910017~020	2009/01/05	Ivan Lin	Update panel thickness
D	LEN15B0243~46	2015/11/03	Ruru	Change Logo
E	C201125	2020-07-30	Fu	$\triangle E \times 5$



Yellow	黃	4
Red	紅	3
Green	綠	2
White	白	1
Wire Color	Conn.	

Out Pin

Pin Assignments
Front View 前視圖

Recommended Panel Cut-Out

AU-04PMMM-SL7AXX

XX: 01~99Meters
01: 01Meter
02: 02Meters99: 99Meters
Cable Length(L): 01~99Meters $\triangle E$ Note:

- * $\textcircled{CC}$ Important Dimension To Check.
- * Waterproof Rate: IP67(Mated)
- * Housing: Thermoplastic, Black
- * Pin: Copper Alloy, Gold Plated
- * Cable: UL2464 24AWG*4C+Drain+Al/My Black, PVC Jacket UV Resistant OD=5.8mm
- $\triangle C \triangle B$ * Use with waterproof cap or dust cap
Panel Thickness Max: 2.5mm
- $\triangle C \triangle B$ * Use without waterproof cap or dust cap
Panel Thickness Max: 3.5mm
- $\triangle C$ * Cable Length Tolerance: 01M: ± 40 mm
02M~05M: ± 60 mm
06M~10M: ± 100 mm
11M~30M: ± 200 mm
31M~99M: ± 500 mm

UNIT:mm	
TOLERANCE	
.X	± 0.25
.XX	± 0.1
.XXX	± 0.05
ANGLES	$\pm 1^\circ$

TITLE O CERES, A-2A, 04P, FRONT FASTENED M, M, MOLDING, SCREW			
SCALE 1:1	SIZE A4	SHEET 1	OF 1
REV. E	WC-REV. A.2	$\textcircled{CC}$: Inspection item	

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO.	DRAWN BY Ruru	DATE 2015-11-03
DWG NO. AU-04PMMM-SL7AXX	CHECKED BY Rita	DATE 2015-11-03
CUSTOMER ALTW	APPROVED BY Lisa	DATE 2015-11-03

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[AU-04PMMM-SL7A01](#) [AU-04PMMM-SL7A02](#) [AU-04PMMM-SL7A05](#) [AU-04PMMM-SL7A10](#)