


REVISION HISTORY			
REV	DESCRIPTION	DATE	APPROVED
-	DCN 49729	03/20	BNK

PRODUCT DATA DRAWING



MATERIAL:

CONNECTORS: KEYED SMA FEMALE BLKHD (SEE TABLE I)
SMA MALE (SF2906-6002)

CABLE: T-FLEX 405 (200-70-139)

STRAIN RELIEF: M23053/5

PERFORMANCE:

IMPEDANCE: 50 OHMS

FREQ. RANGE: DC TO 18.0 GHz.

TABLE I					
PART NUMBER		KEYED SMA FEMALE BLKHD CONNECTOR PART NUMBER			
7029-3408		SF2921-61614-1K (2 X 180°)			
7029-3409		SF2921-61614-2K (2 X 150°)			
7029-3410		SF2921-61614-3K (2 X 120°)			
7029-3411		SF2921-61614-4K (2 X 90°)			
TOLERANCES: AR: X° ±1°0' X°X' ±15'		UNLESS OTHERWISE SPECIFIED 1) ALL DIMENSIONS ARE IN INCHES (MILLIMETERS) 2) ALL DIMENSIONS ARE AFTER PLATING. 3) BREAK CORNERS & EDGES .005 R. MAX. 4) CHAM. 1ST & LAST THREADS. 5) SURFACE ROUGHNESS 63+MIL-STD-10. 6) DIA.'S ON COMMON CENTERS TO BE CONCENTRIC WITHIN .005 T.I.R. 7) REMOVE ALL BURRS		 www.svmicrowave.com	
TOLERANCES		TITLE: KEYED SMA STR. F BLKHD TO SMA STR. M TFLEX405 CABLE ASSEMBLY		7029-3408-3411	
SECTION		DRAWN: JPM 03/30/20			
		CHECKED: BNK 03/30/20			
		APPROVED: BNK 03/30/20		SCALE: 2:1	
				SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[7029-3409](#)