

NOTES:

1) LABEL REQUIREMENT:


- LABELS ARE M23053/5, WHITE. ACCEPTABLE SUBSTITUTION IS DAT-38-292 OR TRANSVINYL (DAT-63-292-2.5).
- MARKING ORIENTATION IS OPTIONAL.

2) TEST REQUIREMENT:

IL @ 1310 nm SHALL BE 2.5 dB MAX PER CONNECTION.

REVISION HISTORY - ALL SHEETS ARE AT THE SAME REVISION

REV	DESCRIPTION	DATE	APPROVED
-	INITIAL RELEASE	2017/11/13	



P1	PINOUT DIAGRAM	P2
A1	BLUE	A1
B1	ORANGE	B1
A2	GREEN	A2
B2	BROWN	B2

2	WTTO-0400	CABLE, 4 FIBER 9/125 TACTICAL DISTRIBUTION	17.1 FEET
1	EB4H1000-3445	PLUG ASSY, BLACK ALUM, 4 CH, 1310/1550 SM, TACBEAM 4.5-6.0 MM	2
ITEM NO.	PART NO.	DESCRIPTION	QTY/ LENGTH
		MATERIAL:	
		DFTR/Designer: C. Hoang 2017/10/23	
		Check By: B. Waite 2017/10/24	
		Manufacturing: B. Waite 2017/10/24	
		Market Manager/PLM: Q. Abraham 2017/10/25	
		Configuration Management: L. Brown 2017/11/13	
		DRILLED HOLE DIAMETER TOLERANCE	
		0.000 TO 0.125 0.001 0.251 TO 0.500 0.001 0.126 TO 0.250 0.001 0.501 TO 0.750 0.001	
		DO NOT SCALE DRAWING	
		UNLESS OTHERWISE SPECIFIED	
		DIMENSIONS ARE IN INCHES	
		TOL ON ANGLES 13°	
		1 PL ±1 2 PL ±02 3 PL ±010	
		INTERPRET DIM AND TOL PER	
		ASME 14.5M-1994	
		Copyright © 2017 Amphenol Fiber Systems International.	
		Non published work. All rights reserved.	
		SIZE A	
		CAGE CODE OYPM2	
		DWG NO 2016032301TD-D2	
		REV -	
		SCALE: NONE	
		SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[2016032301TD-D2](#)