



THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN-9A0189~192	2009/04/20	Li Xiu Zhi	Change SR View & Update Note
C	LEN-0C0122~125	2010/11/23	Ivan	Change 前導角 View
D	LEN1480111~114	2014/07/30	Vicky	Update Logo





Conn.



1 CU-18AFFM-LL7000
Color: Black

2 Cable



Pin Assignments
Front View

18	Blue/White	藍/白
17	Light Green	淺綠
16	Green/White	綠/白
15	Brown/White	棕/白
14	Orange/White	橘/白
13	Black/White	黑/白
12	Red/White	紅/白
11	Orange	橘
10	Pink	粉紅
9	Gray	灰
8	Purple	紫
7	Yellow	黃
6	Green	綠
5	White	白
4	Brown	棕
3	Blue	藍
2	Black	黑
1	Red	紅
Conn.	Wire Color	
Pin Out		

CU-18AFFM-LL7AXX

XX : 01~99Meters
01 : 01Meter
02 : 02Meters
:
:
:
99 : 99Meters

Cable Length(L): 01~99Meters

Note:

- * (QC) Important Dimension To Check
- * Waterproof Rate: IP67
- * Housing: Nylon+GF, Black
- * Female Pin: Copper Alloy, Gold Plated
- * Lock Nut: Nylon+GF, Black
- * O-Ring: EPDM, Black
- * Cable: UL2464 24AWG*18C+Drain+Al/My, Black, PVC Jacket, UV Resistant, OD=8.0
- * Cable Length Tolerance: 01M: ±40mm
02M~05M: ±60mm
06M~10M: ±100mm
11M~30M: ±200mm
31M~99M: ±500mm

UNIT:mm	
TOLERANCE	±0.5 mm

TITLE Middle Cable Lock 18Pin F Conn F Pin			
SCALE 1:1	SIZE A4	SHEET 1 OF 1	
REV. D	WC-REV. A.1	(QC): Inspection item	

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY Vicky	DATE 2014-07-30
DWG NO CU-18AFFM-LL7AXX	CHECKED BY Sam	DATE 2014-07-30
CUSTOMER ALTW	APPROVED BY Rita	DATE 2014-07-30

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[CU-18AFFM-LL7A10](#)