








	1	2	3	4	5	6	7	8																									
F	<table><tr><td>8P</td><td>TPU</td><td>6.8</td><td>26</td><td>ASY-A08BFFM-QL8JXX</td></tr><tr><td>Contacts</td><td>Cable Jacket</td><td>Cable OD</td><td>AWG</td><td>Item No.</td></tr></table>				8P	TPU	6.8	26	ASY-A08BFFM-QL8JXX	Contacts	Cable Jacket	Cable OD	AWG	Item No.	REV. A	ECN NO.	DATE 2022-02-23	SIGN Sam Ho	DESCRIPTION Rev.01 to A, Initial Released														
	8P	TPU	6.8	26	ASY-A08BFFM-QL8JXX																												
	Contacts	Cable Jacket	Cable OD	AWG	Item No.																												
E									ASY-AXXBFFM-QL8JXX XX:L=0~99Meters 01:L=1Meters 02:L=2Meters : 99:L=99Meters XX:No. Of Pin																								
	<table><tr><td>Shield Braid</td><td>編織</td><td></td></tr><tr><td>8 Blue</td><td>藍</td><td rowspan="2">Twist</td></tr><tr><td>7 White/Blue</td><td>白/藍</td></tr><tr><td>6 Brown</td><td>棕</td><td rowspan="2">Twist</td></tr><tr><td>5 White/Brown</td><td>白/棕</td></tr><tr><td>4 Green</td><td>綠</td><td rowspan="2">Twist</td></tr><tr><td>3 White/Green</td><td>白/綠</td></tr><tr><td>2 Orange</td><td>橘</td><td rowspan="2">Twist</td></tr><tr><td>1 White/Orange</td><td>白/橘</td></tr></table>					Shield Braid	編織		8 Blue	藍	Twist	7 White/Blue	白/藍	6 Brown	棕	Twist	5 White/Brown	白/棕	4 Green	綠	Twist	3 White/Green	白/綠	2 Orange	橘	Twist	1 White/Orange	白/橘				Note: * RoHS Compliant *  Important dimension * Waterproof rate: IPX8, mated 1m/24h * Connector - Housing: Thermoplastic, Black - Pin: Copper alloy, Gold plated - Shield: Metal - Nut: Metal - Outer mold: Thermoplastic, Black * Cable: CAT 6A, 26#*4P+AL/MY+B, TPU Jacket, OD 6.8mm, GN. * Cable length tolerance: 1M: +50/-0 mm 1M < L ≤ 3M: +100/-0 mm 3M < L ≤ 5M: +150/-0 mm 5M < L ≤ 10M: ±100 mm 10M < L ≤ 20M: ±200 mm 20M < L ≤ 30M: ±300 mm 30M < L ≤ 99M: ±500 mm	
	Shield Braid	編織																															
8 Blue	藍	Twist																															
7 White/Blue	白/藍																																
6 Brown	棕	Twist																															
5 White/Brown	白/棕																																
4 Green	綠	Twist																															
3 White/Green	白/綠																																
2 Orange	橘	Twist																															
1 White/Orange	白/橘																																
<table><tr><td>Pin #</td><td>Wire</td></tr><tr><td colspan="2"></td></tr><tr><td colspan="2">8P</td></tr><tr><td colspan="2">Pin Assignments Front View</td></tr></table>					Pin #	Wire			8P		Pin Assignments Front View																						
Pin #	Wire																																
																																	
8P																																	
Pin Assignments Front View																																	
A	UNIT:mm				TITLE XLOK, A SHLD-0.5A, A08P, CABLE W/O SR		ITEM NO		DRAWN BY Sam Ho		DATE 2022-02-18																						
	TOLERANCE ±0.50mm		SCALE 2:1		SIZE A4		SHEET 1 OF 1		DWG NO ASY-AXXBFFM-QL8W00		CHECKED BY Fred Lee		DATE 2022-02-18																				
	REV. A		WC-REV.		 :Inspection item		Amphenol LTW 安費諾亮泰企業股份有限公司		CUSTOMER ALTW		APPROVED BY Fred Lee		DATE 2022-02-18																				
	1	2	3	4	5	6	7	8	W10814-03-0001A2																								

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[ASY-A08BFFM-QL8J01](#)