




REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	C210383	2021-03-24	Ouyang	B XI

Note: $\triangle B$


- * RoHS Compliant
- * QC Important Dimension
- * Waterproof Rate: IPX8, Unmated 1m/24h
- * Connector
 - Housing: Thermoplastic, Black
 - Pin: Copper Alloy, Gold Plated
- * Nut: Metal / Thermoplastic, Black
- * O-Ring: Rubber, Gray
- * Use Without Waterproof Cap
 - Panel Thickness Max: 4.0mm
- * Use With Waterproof Cap
 - Panel Thickness Max: 3.0mm
- * Gasket and nut are packed separately in PE bag
- * Nut is packed separately in PE bag
- * O-Ring / Gasket and nut are assembled on connectors

UNIT:mm		TITLE
TOLERANCE		X Lok A-Size Receptacle Front Fastened M Conn M Pin 16A
$\pm 0.5\text{mm}$		SCALE 1:1 SIZE A4 SHEET 1 OF 2
REV. B	WC-REV. .0	QC : Inspection item

ITEM NO	DRAWN BY	DATE
DWG NO	Ouyang	2021-01-23
AG-XXPMJS-QC800P	CHECKED BY	DATE
CUSTOMER	Jerry	2021-01-23
ALTW	APPROVED BY	DATE
	Fred	2021-01-23

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.




(AG) I6A AG- XX P M J S- Q C 8 0 0 P

03: 3Pin
04: 4Pin
05: 5Pin

P: Front Fastened
M: Male Connector(公座)
J: Male Pin And Female grounding Pin

8: IP68(防水等級68)
C: Circular Backshell
Q: Push Lock
S: Solder Type

Pin Assignments Front View



3Pin

4Pin

5Pin

UNIT:mm



TOLERANCE

±0.5mm

TITLE
X Lok A-Size Receptacle
Front Fastened M Conn M Pin I6A

SCALE
1:1

SIZE
A4

SHEET
2 OF 2

REV.
B

WC-REV.
.0

QC: Inspection item

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO

DWG NO

CUSTOMER

AG-XXPMJS-QC800P

ALTW

DRAWN BY

CHECKED BY

APPROVED BY

Ouyang

Jerry

Fred

DATE

DATE

DATE

2020-09-07

2020-09-07

2020-09-07

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[AG-05PMJS-QC800P](#)