






THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION
A		2021-05-26	Sam Ho	Rev.01 to A, Initial Released

5 Pin	PVC	6.2	20	LAD-05BMMM-QL8DXX
4 Pin		6.0		LAD-04BMMM-QL8DXX
3 Pin		5.5		LAD-03BMMM-QL8DXX
Contacts	Cable Jacket	Cable OD	AWG	Item No.



5 - -	5 - -	5 Yellow	黃
4 Brown 棕	4 Orange 橘	4 Orange 橘	
3 Red 紅	3 Red 紅	3 Red 紅	
2 - -	2 Brown 棕	2 Brown 棕	
1 Black 黑	1 Black 黑	1 Black 黑	
Pin #	Wire	Pin #	Wire



Note:

- * $\varnothing$ Important Dimension
- * Waterproof Rate: IPX8, Mated 1m/24h
- * Connector
 - Housing: Thermoplastic, Black
 - Pin: Copper Alloy, Gold Plated
 - Outer Mold: Thermoplastic, Transparent Black.
- * Cable: UL21388, PVC Jacket, Black
- * Cable Length Tolerance:

IM: +50/-0 mm
IM < L ≤ 3M: +100/-0 mm
3M < L ≤ 5M: +150/-0 mm
5M < L ≤ 10M: ±100 mm
10M < L ≤ 20M: ±200 mm
20M < L ≤ 30M: ±300 mm
30M < L ≤ 99M: ±500 mm

LAD- XX BMMM-QL8D XX

No. Of Pin

XX: L=0~99Meters
01: L=1Meters
02: L=2Meters
:
99: L=99Meters

UNIT:mm		TITLE
TOLERANCE		XLOK, LED-A-5A, 05P, CABLE W/O SR
±0.50mm		M, M, MOLDING, PUSH LOCK
SCALE	SIZE	SHEET
3:2	A4	1
REV.	WC-REV.	QC: Inspection item
A		

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY	DATE
	Sam Ho	2021-05-11
DWG NO	CHECKED BY	DATE
LAD-XXBMMM-QL8DXX	Fred Lee	2021-05-11
CUSTOMER	APPROVED BY	DATE
ALTW	Fred Lee	2021-05-11

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[LAD-05BMMM-QL8D01](#) [LAD-05BMMM-QL8D02](#) [LAD-05BMMM-QL8D05](#) [LAD-05BMMM-QL8D10](#) [LAD-05BMMM-QL8D01](#) [LAD-05BMMM-QR8D02](#) [LAD-05BMMM-QR8D05](#)