

THIS DRAWING IS SUPPLIED FOR INFORMATION ONLY. DESIGN FEATURES, SPECIFICATIONS AND PERFORMANCE DATA SHOWN HEREON ARE THE PROPERTY OF THE AMPHENOL CORPORATION. NO RIGHTS OF REPRODUCTION ARE IMPLIED. ALL DIMENSIONS ARE SUBJECT TO NORMAL MANUFACTURING VARIATIONS.

CUSTOMER DRAWING

REVISIONS					
REV#	ECN#	REVISION ACTION	REV.BY:	APPR.BY:	DATE
1	--	INITIAL RELEASE	Steven	JL	08/18/2021





订购信息 Ordering Information

PL01 X - 20 0 - 50

Cable Rcpt

Key and Color
"X", Orange
"Y", Black
"U", Yellow
"V", Green
"W", Red

Cable Size
"50"=50mm²
"35"=35mm²
"25"=25mm²



Standard Part List


P/N	Model No	Cable OD
EX-HA008857	PL01X-200-25	13.5+/-0.3
EX-HA008858	PL01Y-200-25	
EX-HA008859	PL01U-200-25	
EX-HA008860	PL01V-200-25	
EX-HA008861	PL01W-200-25	
EX-HA008862	PL01X-200-35	14.5+/-0.5
EX-HA008863	PL01Y-200-35	
EX-HA008864	PL01U-200-35	
EX-HA008865	PL01V-200-35	
EX-HA008866	PL01W-200-35	
EX-HA008867	PL01X-200-50	17.0+/-0.5
EX-HA008868	PL01Y-200-50	
EX-HA008869	PL01U-200-50	
EX-HA008870	PL01V-200-50	
EX-HA008871	PL01W-200-50	

Holder Size

Model	A	B
PL01()-200-25	10.0±0.3	7.5±0.3
PL01()-200-35	12.0±0.3	9.0±0.3
PL01()-200-50	14.0±0.3	10.6±0.3

规格参数(Spec.):

- 工作温度 Operating temperature:-40°C ~ +125°C.
- 额定电流 Current rating:
Power: 50mm²2,200A;
- 额定电压 Operating voltage:
Power: 1000 VDC;
- 耐电压 Dielectric withstanding voltage:
A. 与插座对接后, Pin与铁壳之间
When mated, between pin and metal shell: 5000 VDC.
- 防护等级 Protection class:Mated- IP67, unmated-IP2X.
- 机械寿命 Mating cycle:100 Min.
- 带自动二次锁扣 Automatic Secondary Lock.
- 配对插头 Mating Plug: See drawing "PL18-200"."PL28-200"



Amphenol Technical Products International Asia.

第三角投影 THIRD ANGLE PROJECTION	页面 SHEET	幅面 SIZE	版次 REV.	比例 SCALE	PART NAME: PwrLok 8mm Rcpt	
	1 OF 1	A4	1	--		
签名 SIGNATURE	日期 DATE	UNLESS OTHERWISE SPECIFIED 1) All dimensions are in metric(mm). 2) Tolerances are as follows: 1.PL DEC ± 1.00 2.PL DEC ± 0.50 3.PL DEC ± 0.20 Angles ±1°			DWG NO: PL01(X)-200-XX	
制图 DRAWN	Steven	08/18/2021				
审核 CHECKED						
批准 APPROVAL						
					CUST PART #	CUST REV.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

[PL01U-200-25](#) [PL01U-200-35](#) [PL01U-200-50](#) [PL01V-200-25](#) [PL01V-200-35](#) [PL01V-200-50](#) [PL01W-200-25](#)
[PL01W-200-35](#) [PL01W-200-50](#) [PL01X-200-25](#) [PL01X-200-35](#) [PL01X-200-50](#) [PL01Y-200-25](#) [PL01Y-200-35](#) [PL01Y-200-50](#)