


NOTES:

1. MATERIALS AND FINISHES:
BODIES - BRASS, NICKEL PLATING
CONTACT - BeCu, SILVER PLATING
INSULATOR - PTFE, NATURAL
2. ELECTRICAL:
A. IMPEDANCE: 50 OHM
3. MECHANICAL:
A. DURABILITY: 500 CYCLES MIN.
B. TEMPERATURE RANGE: -65° C TO +165° C
4. PACKAGING:
A. QUANTITY: SINGLE PACK
B. MARKING: BAG TO BE MARKED
"AMPHENOL RF, 4525, AND DATE CODE"
C. GASKET, LOCK WASHER AND HEX ARE PACKAGED LOOSE.


THIRD ANGLE PROJ.

REVISIONS

REV	DESCRIPTION	DATE	ECO	APPR
--	RELEASE TO MFG.	--	--	--
T	REDRAWN IN PRO-E & COD SHEET ADDED	03-Sep-15	50266	AAP



SCALE 1.500



RECOMMENDED MOUNTING
HOLE DIMENSIONS

CUSTOMER OUTLINE DRAWING

ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN METRIC AND TOLERANCES ARE: <0.5mm 0.5 - 6mm 6 - 30mm 30 - 120mm ANGLES ± 0.05mm ±0.1mm ±0.2mm ± 0.3mm ±1° NOTICE - These drawings, specifications, or other data (1) are, and remain the property of Amphenol corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. the furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights to permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.	MATERIAL	DRAWN STAR	DATE 03-Sep-15	TITLE BNC STR JACK TO BNC STR BHD JACK ADAPTER 50 OHM NON-PRESSURIZED		Amphenol RF www.amphenolrf.com	
	REFERENCE	ENGINEER D.ROYCE	DATE 17-Oct-89			DRAWING NO. 4525	
	CONFIGURATION LEVEL: In Work	APPROVED S.HSIEH	DATE 03-Sep-15			SCALE: 7.0:1.0 SHEET 2 OF 2	
	FINISH	CAD FILE	DWG SIZE B		REV T	ITEM NO. 4525	PART NO. 4525

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[000-4525](#)