







NOTES:

1. MATERIALS AND FINISHES
BODY - BRASS, NICKEL PLATING
CONTACT - BERYLLIUM COPPER, SILVER PLATING
INSULATOR - PTFE, NATURAL
2. ELECTRICAL:
A. IMPEDANCE: 50 OHM
B. FREQUENCY RANGE: DC 0-11 GHz
C. DIELECTRIC WITHSTANDING VOLTAGE: 1500 VRMS, MIN.
3. MECHANICAL:
A. DURABILITY: 500 CYCLES MIN.
B. TEMPERATURE RANGE: -40°C to +85°C

THIRD ANGLE PROJ. 

REVISIONS

REV	DESCRIPTION	DATE	ECO	APPR
B	SEE SHEET 1	18-Aug-05	--	ROCKY
B1	SEE SHEET 1	19-Sep-05	--	ROCKY
N	REDRAWN TO UPDATE FORMAT	19-Dec-08	47354	

RECOMMENDED
CABLE STRIPPING DIM'S

CUSTOMER OUTLINE DRAWING

ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN METRIC AND TOLERANCES ARE:
0.5 - 6mm ±0.1mm 6 - 30mm ±0.2mm 30 - 120mm ±0.3mm ANGLES ±1°

NOTICE - These drawings, specifications, or other data (1) are, and remain the property of Amphenol Corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. The furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights or permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.

MATERIAL

REFERENCE

FINISH

DRAWN
EDWARDENGINEER
SCOTTAPPROVED
SCOTT

CAD FILE

F:\DWG\CNPD\79075-NSZ

DATE
19-Sep-05DATE
19-Sep-05DATE
19-Sep-05TITLE
TNC ANGLE PLUG
FOR 58/U CABLE

SCALE: 2.5/1

DWG SIZE
BCODE ID
74868REV
NSHEET
2 OF 2Amphenol RF
Danbury CT USA, Tainan Taiwan, Shenzhen China
www.amphenolrf.comDRAWING NO.
79075ITEM NO.
79075PART NO.
79075

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[79075](#) [000-79075](#)