




REVISIONS		
ISS	ZONE	DESCRIPTION\PER REQUEST\DATE



CONFIGURATION CONTROL:
NO CHANGES PERMITTED TO DRAWING WITHOUT
PPAP QUALIFIED CUSTOMER APPROVAL



NOTES: FINISH (PLATING THICKNESS IN MICRO-INCHES)
1. BRASS PER QQ-B-626, ALLOY 360, 1/2 H
; JIS H3250 C 3604BD OR EQUIVALENT
2. NICKEL PL. 60 MIN. THICK OVER COPPER STRIKE
3. GOLD PL. 30 MIN. THICK OVER NICKEL PL. 100 MIN. THICK
OVER COPPER STRIKE
4. TEFLON MIL-P-19468 OR EQUIVALENT
5. COPPER PER ASTM B-75 ALLOY C12200 OR EQUIVALENT
6. PBT(WITH 15% GLASS FIBER) PER CHANG CHUN GRADE 4115202
OR EQUIVALENT




1. CRIMPED FERRULE
HEX CRIMP SIZE .128"
2. CRIMPED CONTACT PIN
SQ. CRIMP SIZE 0.7 MM



TABLE

KEY CODING	D/N	P/N	LOCK COVER
A	FK1321AW-007-NT30G-50	FA1-NASP-C01-0	FKLC10201A
B	FK1321BW-007-NT30G-50	FA1-NBSP-C01-0	FKLC10202A
C	FK1321CW-007-NT30G-50	FA1-NCSP-C01-0	FKLC10203A
D	FK1321DW-007-NT30G-50	FA1-NDSP-C01-0	FKLC10204A
E	FK1321EW-007-NT30G-50	FA1-NESP-C01-0	FKLC10205A
F	FK1321FW-007-NT30G-50	FA1-NFSP-C01-0	FKLC10206A
G	FK1321GW-007-NT30G-50	FA1-NGSP-C01-0	FKLC10207A
H	FK1321HW-007-NT30G-50	FA1-NHSP-C01-0	FKLC10208A
I	FK1321IW-007-NT30G-50	FA1-NISP-C01-0	FKLC10209A
K	FK1321KW-007-NT30G-50	FA1-NKSP-C01-0	FKLC10210A
Z	FK1321ZW-007-NT30G-50	FA1-NZSP-C01-0	FKLC10211A



8	FERRULE	NOTE 5	NOTE 2	1	FKFR00101A	DIMENSIONS ARE IN MILLIMETERS UNLESS OTHERWISE SPECIFIED TOLERANCES 0.5-6 = ±0.2 6-30 = ±0.4 30-120 = ±0.6 120-315 = ±1 315-1000 = ±1.6 1000-2000 = ±2.4				PART NO. FA1-NXSP-C01-0		Amphenol Danbury,CT,USA-Tainan,Taiwan-Shenzehn,China	
7	CONTACT PIN	NOTE 1	NOTE 3	1	FKCP00101A					APPROVED DATE 10-04-01'			
6	RING	NOTE 1	NOTE 2	1	FKLR00101A					CHECKED DATE 10-04-01'		DRAWING NO. KJ-FK1321XX-007-NT30G-50	
5	LOCK COVER	NOTE 6		1	SEE TABLE					DRAWN DATE 10-04-01'		FILE NO. F:\DWG\FK\FA1\NXSP\C01\0	
4	BARREL	NOTE 1	NOTE 2	1	FKBR00101B					ANGELA			
3	INSULATOR	NOTE 4	NATURAL	1	FKNS00201A								
2	INSULATOR	NOTE 4	NATURAL	1	FKNS00101A								
1	MAIN BODY	NOTE 1	NOTE 2	1	FKMB00101A								
NO.	DESCRIPTION	MATERIAL	FINISH	Q'TY	DRAWING NO.	SCALE	2/1	ISSUE	1				

Amphenol

Danbury,CT,USA-Tainan,Taiwan-Shenzehn,China

FAKRA SMB CRIMP PLUG
(FOR RG-174/U, 188A/U, 316/U CABLE)

DRAWING NO.
KJ-FK1321XX-007-NT30G-50

FILE NO. F:\DWG\FK\FA1\NXSP\C01\0

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[FA1-NLSP-C01-0](#)