



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF AMPHENOL CABLES ON DEMAND. ANY REPRODUCTION OR DISCLOSURE TO THIRD PARTIES, IN PART OR WHOLE, WITHOUT THE EXPRESS WRITTEN PERMISSION OF AMPHENOL CABLES ON DEMAND IS PROHIBITED.

REVISIONS		DATE	APPROVED
REV.	DESCRIPTION		
A	NEW RELEASE	03MAY2023	



NOTE:

1. CURRENT RATING: 1A MAX.
2. DIELECTRIC WITHSTANDING VOLTAGE: 500V(AC) FOR 1 MINUTE
3. CONTACT RESISTANCE: 30mΩ MAX.
4. INSULATION RESISTANCE: 1000MΩ MIN. AT DC 500V
5. MATING FORCE: 13.5 KG MAX.
6. UNMATING FORCE: 3.7KG MIN.
7. TEMPERATURE RANGE: -55°C~+105°C



UNLESS OTHERWISE SPECIFIED  
DIMENSIONS ARE IN INCHES  
TOLERANCES ARE:

DECIMALS	ANGLES
±.X	±.X°
±.XX	
±.XXX	

THIRD ANGLE PROJECTION



EAR NO.

APPROVALS

DRAWN

CHECKED

RESP ENG

DATE

XF

HYJ

**Amphenol Cables on Demand**

20 VALLEY ST. ENDICOTT, NY 13760

**D-SUB 78P CONNECTOR MALE**

SIZE	DWG. NO.	REV.
A	CN-DSUBHD78PN-400	A

NOTES: UNLESS OTHERWISE SPECIFIED

4

3

4

2

1

SCALE: N/A SHEET 1 OF 1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[CN-DSUBHD78PN-000](#)