


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF AMPHENOL CABLES ON DEMAND. ANY REPRODUCTION OR DISCLOSURE TO THIRD PARTIES, IN PART OR WHOLE, WITHOUT THE EXPRESS WRITTEN PERMISSION OF AMPHENOL CABLES ON DEMAND IS PROHIBITED.

REVISIONS		DATE	APPROVED
REV. A	DESCRIPTION NEW RELEASE	3/DEC/2013	
A1	Added ACP P/N to the table.	24/Oct/2019	




Reverse Polarity TNC Male

Reverse Polarity TNC Female

LENGTH & P/N Table

LENGTH	CUSTOMER P/N
3FT(914±30mm)	CO-058TNCMFRP-003
6FT(1829±40mm)	CO-058TNCMFRP-006
10FT(3048±40mm)	CO-058TNCMFRP-010
15FT(4572±50mm)	CO-058TNCMFRP-015
25FT(7620±100mm)	CO-058TNCMFRP-025



SECTION A-A

- NOTES:
- CABLE:[20AWG(19/0.18±0.008mm)\*1C+AL/MYLAR +BRAID(16\*8/0.12±0.008mm)]TINNED COPPER INSULATION:PE OD= 2.95±0.10mm COLOR:TRANSPARENT JACKET:HALF MATTE PVC LOW TOXIC; OD=Ø5.0±0.15mm COLOR:UL813 BLACK
  - CONNECTOR:Reverse Polarity TNC Male
  - OPEN/SHORT MISS WIRE TEST 100%
  - CONDUCTOR RESISTANCE  $\leq$  36.7Ω/km
  - INSULATION RESISTANCE  $\geq$  2MΩ DC300V 0.01Sec
- ALL MATERIALS SHALL ACCORD WITH ROHS STANDARD.

**PIN OUT:**

CENTER	CENTER
SHELL	SHELL



UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE:		E&R NO.		Amphenol Cables on Demand	
DECIMALS	ANGLES	APPROVALS	DATE	20 VALLEY ST. ENDICOTT, NY 13760	
.X	±X	LF	3/DEC/2013	RG58C/U RP TNC M/RP TNC F	
.XX	±XX	CHECKED	BA		
.XXX	±XXX	RESP ENG	3/DEC/2013		
THIRD ANGLE PROJECTION		MFG ENG		SIZE DWG. NO.	CO-058TNCMFRP-XXX
				A	
CAD FILE				SCALE	SHEET
					OF

NOTES: UNLESS OTHERWISE SPECIFIED

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[CO-058TNCMFRP-003](#) [CO-058TNCMFRP-006](#) [CO-058TNCMFRP-010](#) [CO-058TNCMFRP-015](#) [CO-058TNCMFRP-025](#)