



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF AMPHENOL CABLES ON DEMAND. ANY REPRODUCTION OR DISCLOSURE TO THIRD PARTIES IN PART OR WHOLE, WITHOUT THE EXPRESS WRITTEN PERMISSION OF AMPHENOL CABLES ON DEMAND IS PROHIBITED.

REV.		REVISIONS		DATE	APPROVED
A		NEW RELEASE		22/Oct/09	



NOTES:

1. CABLE:126AWG(7/0.16±0.008mm)*1C
+BRAID(16*4/0.12±0.008mm)TINNED COPPER
INSULATION:PE OD= 1.52±0.07mm ;COLOR:TRANSPARENT
JACKET:HALF MATTE PVC LOW TOXIC;OD=Ø2.54±0.10mm
COLOR:UL813 BLACK.
 2. MARKING:RG-174/U COAXIAL CABLE ROHS
 3. CONNECTOR:SMA Male GOLD-PLATING
 4. OPEN/SHORT MISS WIRE TEST 100%
 5. CONDUCTOR RESISTANCE ≅150Ω/km
 - 6.INSULATION RESISTANCE ≅2MΩ.DC300V 0.01Sec
- ALL MATERIALS SHOULD ACCORD WITH ROHS STANDARD.



SECTION A-A

LENGTH & P/N Table

LENGTH	CUSTOMER P/N
6 INCH(152±15mm)	CO-174SMAZBNC-000.6
1FT(305±20mm)	CO-174SMAZBNC-001
5FT(1524±30mm)	CO-174SMAZBNC-005
7.5FT(2286±40mm)	CO-174SMAZBNC-007.5
10FT(3048±40mm)	CO-174SMAZBNC-010

PIN OUT:

CENTER	CENTER
SHELL	SHELL



NOTES: UNLESS OTHERWISE SPECIFIED

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE:				Amphenol Cables on Demand 20 VALLEY ST. ENDICOTT, NY 13760			
EARS NO.		APPROVALS		DATE		SIZE	
DRAWN		L.F.		22/Oct/09		DWG. NO.	
CHECKED		BA		22/Oct/09		CO-174SMAZBNC-XXX	
THIRD ANGLE PROJECTION		RESP ENG				REV.	
MFG ENG						A0	
C/D FILE:		SCALE		SHEET		OF	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[CO-174SMAZBNC-000.6](#) [CO-174SMAZBNC-001](#) [CO-174SMAZBNC-005](#) [CO-174SMAZBNC-007.5](#) [CO-174SMAZBNC-010](#)