



5 Sealing Nut



4 Seals




3 Clamping Nut




2 Gasket




1 Nut




Recommended Panel Cut-Out




D




15.0



Section A-A



52.1 (REF.)




D


Note:

- * Waterproof Rate: IP68
- * Screw Nut: Nylon, Gray
- * Clamp Ring: Nylon, Gray
- * Sealing Nut: Nylon, Gray
- * Gasket: EPDM, Black
- * Seals: EPDM, Black
- * Panel Thickness: 6.2mm max
- * Cable Range: $\varnothing 18 \sim \varnothing 13$ mm
- * Spanner Size:
 - ① Screw Nut: 33mm
 - ③ Body: 32.5mm
 - ⑤ Sealing Nut: 35mm

REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN-6A0003	2006/10/04	Rita	Change Cable Range
C	LEN-6C0042	2006/12/06	Jerry	Modify Note
D	LEN1570054	2015/06/01	Ruru	Change Logo



UNIT: mm



TOLERANCE
.X ± 0.25
.XX ± 0.1
.XXX ± 0.05
ANGLES $\pm 1^\circ$

TITLE

M25 Cable Gland Assy
Gray For Long Type

SCALE 3:5

SIZE A4

SHEET 1 OF 1

REV. D

WC-REV. A.1

QC: Inspection item

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO

CSG-25M001

DWG NO

CSG-25M001

CUSTOMER

ALTW

DRAWN BY

Ruru

CHECKED BY

Rita

APPROVED BY

Lion

DATE

2015-06-01

DATE

2015-06-01

DATE

2015-06-01

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[CSG-25M001](#)