





THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF AMPHENOL CABLES ON DEMAND. ANY REPRODUCTION OR DISCLOSURE TO THIRD PARTIES, IN PART OR WHOLE, WITHOUT THE EXPRESS WRITTEN PERMISSION OF AMPHENOL CABLES ON DEMAND IS PROHIBITED.

REV.	DESCRIPTION	DATE	APPROVED
A	NEW RELEASE	07/Feb/2007	
A1	Add Hex.Nut	5/Dec/2007	
A2	Add wiring color	13/JAN/2012	
A3	Add 3FT Length	25/JAN/2018	
A4	Add 50FT Length	14/JAN/2020	



LENGTH	PIN	Cable Color
2.5FT ±1 inch	CS-DSPMHD15MF-002.5	GREY
3FT ±1.2 inch	CS-DSPMHD15MF-003	GREY
5FT ±2 inch	CS-DSPMHD15MF-005	GREY
6FT ±2 inch	CS-DSPMHD15MF-006	GREY
10FT ±3 inch	CS-DSPMHD15MF-010	GREY
12FT ±3 inch	CS-DSPMHD15MF-012	GREY
15FT ±3 inch	CS-DSPMHD15MF-015	GREY
25FT ±4 inch	CS-DSPMHD15MF-025	GREY
50FT ±8 inch	CS-DSPMHD15MF-050	GREY

PIN OUT:		
Male	Female	Color
PIN1	PIN1	Black
PIN2	PIN2	Brown
PIN3	PIN3	Red
PIN4	PIN4	Orange
PIN5	PIN5	Yellow
PIN6	PIN6	Green
PIN7	PIN7	Blue
PIN8	PIN8	Purple
PIN9	PIN9	Gray
PIN10	PIN10	White
PIN11	PIN11	Pink
PIN12	PIN12	Light Green
PIN13	PIN13	Black/White
PIN14	PIN14	Brown/White
PIN15	PIN15	Red/White
SHIELD	SHIELD	Drain Wire



UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE:	
DECIMALS	ANGLES
.X ±.X	±.X°
.XX ±.XX	
.XXX ±.XXX	



Amphenol Cables on Demand
20 VALLEY ST. ENDCOTT, NY 13760

ASM CBL Premium High Density
15PIN D-Sub MF

APPROVALS	DATE	SIZE	DWG. NO.	REV.
DRAWN LF	25/JAN/2018	A	CS-DSPMHD15MF-XXX	A4
CHECKED BA	25/JAN/2018			
RESP ENG				

NOTES: UNLESS OTHERWISE SPECIFIED

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[CS-DSPMHD15MF-050](#) [CS-DSPMHD15MF-002.5](#) [CS-DSPMHD15MF-006](#) [CS-DSPMHD15MF-010](#) [CS-DSPMHD15MF-015](#) [CS-DSPMHD15MF-025](#)