



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF AMPHENOL CABLES ON DEMAND. ANY REPRODUCTION OR DISCLOSURE TO THIRD PARTIES, IN PART OR WHOLE, WITHOUT THE EXPRESS WRITTEN PERMISSION OF AMPHENOL CABLES ON DEMAND IS PROHIBITED.

REVISIONS		DATE	APPROVED
REV.	DESCRIPTION		
A	NEW RELEASE	07-Feb-2007	
A1	Add wiring color	13-Jan-2012	
A2	Add Length: 6.5FT	29-Aug-2017	



4-40thread(UNC)

4X THUMBSCREW

LENGTH



Amphenol Cables on Demand




D-SUB


15PIN Male

D-SUB


15PIN Male



Drain Wire Soldered



0.256



Steel Box

Drain Wire Soldered

LENGTH & P/N Table

LENGTH	P/N	Cable Color
2.5FT ±1 inch	CS-DSPMHD15MM-002.5	GREY
5FT ±2 inch	CS-DSPMHD15MM-005	GREY
6FT ±2 inch	CS-DSPMHD15MM-006	GREY
6.5FT ±2 inch	CS-DSPMHD15MM-006.5	GREY
10FT ±3 inch	CS-DSPMHD15MM-010	GREY
12FT ±3 inch	CS-DSPMHD15MM-012	GREY
15FT ±3 inch	CS-DSPMHD15MM-015	GREY
25FT ±4 inch	CS-DSPMHD15MM-025	GREY

PIN OUT:


Male	Male	Color
PIN1	PIN1	Black
PIN2	PIN2	Brown
PIN3	PIN3	Red
PIN4	PIN4	Orange
PIN5	PIN5	Yellow
PIN6	PIN6	Green
PIN7	PIN7	Blue
PIN8	PIN8	Purple
PIN9	PIN9	Gray
PIN10	PIN10	White
PIN11	PIN11	Pink
PIN12	PIN12	Light Green
PIN13	PIN13	Black/White
PIN14	PIN14	Brown/White
PIN15	PIN15	Red/White
SHIELD	SHIELD	Drain Wire



UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE IN INCHES
TOLERANCES ARE:

TERMS	ANGLES
X	±X°
.XX	±.XX
.XXX	±.XXX

THIRD ANGLE PROJECTION



Amphenol Cables on Demand

20 VALLEY ST., ENDICOTT, NY 13760

ASM CBL Premium High Density
15PIN D-Sub MM

QAD FILE:

EAR NO.		ASME Cables on Demand 20 VALLEY ST. ENDICOTT, NY 13760				
APPROVALS	DATE					
DRAWN	LF					
CHECKED	BA					
RESP ENG	29/Aug/2017	ASME CBL Premium High Density 15PIN D-Sub MM				
WFG ENG		SIZE	DWG. NO.	CS-DSPMHD15MM-XXX		REV.
	A					A2
		SCALE	SHEET	OF		

NOTES: UNLESS OTHERWISE SPECIFIED

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[CS-DSPMHD15MM-002.5](#) [CS-DSPMHD15MM-005](#) [CS-DSPMHD15MM-006](#) [CS-DSPMHD15MM-010](#) [CS-](#)
[DSPMHD15MM-012](#) [CS-DSPMHD15MM-015](#)