




#### NOTES: (c)

1. HOOD + COVER: PBT UL 94 V-0; BLACK
2. CABLE STRAIN RELIEF: STEEL; NICKEL PLATED
3. PRESS INSERT: ABS UL 94 V-0; BLACK
4. SHORT SCREWS: STEEL; NICKEL PLATED
5. LENS HEAD SCREWS: STEEL; NICKEL PLATED

#### TECHNICAL DATA: (b)

- TEMPERATURE RANGE: -40°C to + 125°C



CABLE STRAIN RELIEF (1x)



LENS HEAD SCREW (4x)



SHORT SCREW (2x)



PRESS INSERT (1x)

RoHS compliant

(b)

THIS DRAWING MAY NOT BE COPIED OR  
REPRODUCED IN ANY WAY, AND MAY NOT  
BE PASSED ON TO A THIRD PARTY WITHOUT  
WRITTEN PERMISSION.  
OWNERSHIP AND COPYRIGHT OF CONEC GmbH

DO NOT ALTER CAD DRAWING BY HAND

| rev.  | description | date     | name    |
|-------|-------------|----------|---------|
| 5 x c | A5607       | 14.04.15 | M.H.    |
| 3 x b | A5307       | 25.08.14 | E.Mick. |
| a     | Original    |          |         |

| tolerance  |       | dim. in mm |                 |
|------------|-------|------------|-----------------|
| date       | name  | drawn      | appd.           |
| 08.07.2002 | Parei | 08.07.2002 | E. Mickenbecker |
| norm       | d-old |            |                 |

**CONEC®**

|                                                   |           |
|---------------------------------------------------|-----------|
| scale:                                            | 2:1       |
| material:                                         | SEE NOTES |
| title:                                            |           |
| PLASTIC HOOD<br>9pos.<br>with straight cable exit |           |
| dwg no:                                           | DIN-A3    |
| (c) 16K1A707                                      | sh: 1     |
| part no: 165X13369X / 600X10009XS                 |           |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[165X13369X](#)