




Notes:

1. Electrical:
 - Meets EIA/TIA-568-B.2 Cat.5e Specification
 - Connector Operating Temperature: -40° C to +85° C
2. Materials and Finish:
 - Coupling Ring: Zinc Die-Cast, Nickel Plated
 - Plug Housing: Zinc Die-Cast, Nickel Plated
 - Interfacial Seal: Silicone, Color: White
 - Cable Gland: Brass, Nickel Plated
 - Cable Gland Seal: NBR, Color: Black
 - RJ45 Plug Metal Shell: Copper Alloy, Nickel Plated
 - ⓑ RJ45 Plug Plastic Housing: Clear Polycarbonate UL94 V-2
 - RJ45 Plug Contacts: Phosphor Bronze, Finish: 50 u" Gold min. over Nickel
 - Cable: See Part Number Table
3. IP67 rated on IP67 side when fully mated with the appropriate mating connector
4. RoHS compliant

Cable Length L	Part Number			
	Cat. 5e Outdoor STP 4 Pair, AWG24 Solid Black Cable	Cat. 5e Outdoor UTP 4 Pair, AWG24 Solid Black Cable	Cat. 5e STP 4 Pair, AWG24 Solid Black Cable	Cat. 5e UTP 4 Pair, AWG24 Solid Black Cable
2 m	17-102044	17-102074	17-102104	17-102134
4 m	17-102054	17-102084	17-102114	17-102144
5 m	17-102064	17-102094	17-102124	17-102154

Note: Special cable length are available please contact factory; SPT: Shielded Twisted Pair; UTP: Unshielded Twisted Pair

Directive 2002/95/EC RoHS Compliant

THIS DRAWING MAY NOT BE COPIED, REPRODUCED, OR REPRODUCED IN ANY WAY AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC CORPORATION.	Customer:			Tolerance Unless otherwise specified			Scale: 1.8:1	Dim. in meter
	Name	Title	Approval Date	Dimensional: Angles			Material: See Notes	
				2010	Date	Name	RJ45 Cat. 5e Ethernet Patch Cord Industrial to Industrial Nickel Plated Zinc Die-Cast Version	
				Draw.	May 28	Vincent Ke		
				Appd.	May 28	J. Chaudry		
			Norm			Drawing No.: 17K1A170		DIN A3
			Vincent Ke	D-old		Part No.: SEE P/N ABOVE		Sheet 1/1
	b	1 x b	Sep/22/2011					
	a	original						
	Rev.	Changes	Date	Name				

CONEC®

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[17-102104](#)