





REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN-8A0183	2008/09/15	Shin	Add Notes
C	LEN1740945	2017/04/11	Vicky	Update Logo
D	CI90310	2019/03/11	Ruru	Modify Note



With Liquid Glue

1 Connector

2 Nut

Gasket 3

Note:

* Important Dimension



* Waterproof Rate: IP67, Unmated

* Housing: Thermoplastic, Black

* Pin: Copper Alloy, Gold Plated

* Nut: Thermoplastic, Black

* Gasket: Rubber, Black

 * Use Waterproof Cap or Dust Cap
Panel Thickness Max: 3.0mm * Use without Waterproof Cap or Dust Cap
Panel Thickness Max: 4.0mm* Gasket and Nut are packed separately
in PE bags.Recommended
Panel Cut-OutPin Assignments
Front View

UNIT:mm	
TOLERANCE	
.X	±0.25
.XX	±0.1
.XXX	±0.05
ANGLES	±1°

TITLE Lock Type Connector For Panel Mount 3Pin Male Connector Male Pin(20A)			
SCALE 1:1	SIZE A4	SHEET 1 OF 1	
REV. D	WC-REV. A.3	Inspection item	

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO DC-03PMMS-LC7001	DRAWN BY Ruru	DATE 2019-03-11
DWG NO DC-03PMMS-LC7001	CHECKED BY Rita	DATE 2019-03-11
CUSTOMER ALTW	APPROVED BY Max	DATE 2019-03-11

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[1DC-03PMMS-LC7001](#)