





Pin Assignments
Front View 前視圖

Orange	橙	4
Red	紅	3
Brown	棕	2
Black	黑	1
Wire Color		Conn.
Pin Out		

DC-04AFFM-SL7AXX

XX:01~99Meter
01:01Meter
02:02Meters
:
99:99Meters

Note:

- * @@Important Dimension
- * Waterproof Rate: IP67
- * Housing: Nylon+GF, Black
- * Pin: Copper Alloy, Gold Plated
- * Cable: UL2464 16AWG*4C+AL/My, PVC Jacket (UV Resistant), OD=7.5mm, Black
- * Cable Length Tolerance: 01M:40mm
02M~05M:60mm
06M~10M:100mm
11M~30M:200mm
31M~99M:500mm

UNIT:mm		TITLE		ITEM NO		DRAWN BY		DATE	
TOLERANCE		Screw Type Cable Assembly-180°		DC-04AFFM-SL7AXX		Ruru		2013/06/24	
±0.5mm		4Pin Female Connector Female Pin(20A)		CUSTOMER		Vicky		2013/06/24	
		SCALE Free		ALTW		APPROVED BY		Maslow	
		SHEET 1 OF 1						2013/06/24	
		REV. C							
		SIZE A4							
		QC :Inspection Item							

Amphenol LTW
安費諾亮泰企業股份有限公司

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[1DC-04AFFM-SL7A01](#)