

1		2		3		4		5		6		7		8	
REV. A		ECN NO. LTD-000003336		DATE 2010/12/01		SIGN Ann		DESCRIPTION NEW ITEM							

1

2

3

4

5

6

7

8

9

10

11

12

MPin

FPin

Conn. Pin Assignments Front View

ALTW

DCC. DEPT. CONFIDENTIAL

2010.12.01

ISSUED

12	Drain	地線	(24AWG)	Twist對線
11	Brown	棕	(24AWG)	
10	Black	黑	(24AWG)	
9	Gray	灰	(24AWG)	
8	Blue	藍	(24AWG)	Twist對線
7	Green	綠	(24AWG)	
6	Yellow	黃	(24AWG)	Twist對線
5	White	白	(24AWG)	
4	Red	紅	(24AWG)	Twist對線
3	Blue	藍	(16AWG)	
2	Brown	棕	(16AWG)	
1	Green/Yellow	綠/黃	(16AWG)	
Conn.	Wire Color			
Pin Out				

UNIT:mm

TOLERANCE

±0.5 mm

TITLE

Cable Connector 90° FConn 3MPin(20A)+9FPin(5A)

SCALE Free

SHEET 1 OF 1

REV. A

SIZE A4

QC :Inspection Item

Amphenol LTW

安費諾亮泰企業股份有限公司

ITEM NO

DWG NO DCD-12AFEM-LR7AXX

CUSTOMER ALTW

DRAWN BY Enoch

CHECKED BY Jimmy

APPROVED BY Win

DATE 2009/12/30

DATE 2009/12/30

DATE 2009/12/30

44.1

49.8REF.

ø28.5

① DCD-12AFEM-LR7000 Color: Black

Conn.

② Cable

DCD-12AFEM-LR7AXX

XX:01~99Meter
01:01Meter
02:02Meters
⋮
99:99Meters
Cable Length(L):01~99Meters

② Cable

DCD-12AFEM-LR7AXX

XX:01~99Meter
01:01Meter
02:02Meters
⋮
99:99Meters
Cable Length(L):01~99Meters

Note:

* @Important Dimension To Check.

* Waterproof Rate: IP67

* Connector: Nylon+GF, Black

* Pin: Copper Alloy, Gold Plated

* Cable: UL2464 (24AWG*4P+D+AL/MY)+16AWG*3C+F+P, Black, PVC Jacket, UV Resistant, OD=11.0mm.

* Cable Length Tolerance: 01M±40mm
02M~05M:±60mm
06M~10M:±100mm
11M~30M:±200mm
31M~99M:±500mm

ALTW

CONFIDENTIAL

2010.12.01

R&D DEPT.

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[DCD-12AFEM-LR7A10](#) [DCD-12AFEM-LR7A02](#) [DCD-12AFEM-LR7A05](#) [DCD-12AFEM-LR7A01](#)