




REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN1380137-140	2013/08/07	Ruru	Modify the SR & Tolerance & Change Logo




DCU-08AFDM-LL7000

DCU-08AFDM-LL7BXX

XX:01~99Meter
01:01Meter
02:02Meters

99:99Meters

Cable Length(L):01~99Meters



Conn.
Pin Assignments
Front View

8	Brown	16AWG	棕
7	Green/Yellow	16AWG	綠 / 黃
6	Blue	16AWG	藍
5	Red	24AWG	紅
4	Green	24AWG	綠
3	White	24AWG	白
2	Blue	24AWG	藍
1	Drain		地線
Conn.	Wire Color		
Pin Out			

Twist

Twist

Note:

- * $\varnothing$ Important Dimension To Check
- * Waterproof Rate: IP67
- * Connector: Nylon+GF, UL94V-0, Black
- * Pin: Copper Alloy, Gold Plated
- * O-Ring: Silicone, Gray
- * Lock Nut: Nylon+GF, Black
- * Cable: UL2586 (24#*1P+A)*2C+16#*3C+Drain+Al/Mylar, PVC Jacket, UV Resistant, OD=Ø10.0mm, Black
- * Cable Length Tolerance: 01M±40mm
02M~05M:±60mm
06M~10M:±100mm
11M~30M:±200mm
31M~99M:±500mm

UNIT:mm	
TOLERANCE	± 0.5 mm $\triangle$

TITLE Large Size, Lock Type FConn. 3FPin(20A)+5MPin(2A)			
SCALE 1:1	SIZE A4	SHEET 1 OF 1	
REV. B	WC-REV. B.2	$\varnothing$ Inspection item	

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY Ruru	DATE 2013-08-20
DWG NO DCU-08AFDM-LL7BXX	CHECKED BY Rita	DATE 2013-08-20
CUSTOMER ALTW	APPROVED BY Maslow	DATE 2013-08-20

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[DCU-08AFDM-LL7B05](#) [DCU-08AFDM-LL7B02](#) [DCU-08AFDM-LL7B10](#) [DCU-08AFDM-LL7B01](#)