




DCU-08AMEM-LL7BXX

XX: 01~99Meter
01: 01Meter
02: 02Meters

99:99Meters

Cable Length(L):01~99Meters



Conn.
Pin Assignments
Front View

8	Brown	16AWG	棕
7	Green/Yellow	16AWG	綠 / 黃
6	Blue	16AWG	藍
5	Red	24AWG	紅
4	Green	24AWG	綠
3	White	24AWG	白
2	Blue	24AWG	藍
1	Drain		地線
Conn.	Wire Color		
	Pin Out		

Twist

Twist

Note:

- *  Important Dimension To Check
- * Waterproof Rate: IP67
- * Connector: Nylon+GF, UL94V-0, Black
- * Pin: Copper Alloy, Gold Plated
- * Cable: UL2586 (24#*1P+A)*2C+16#*3C+Drain+Al/Mylar,
PVC Jacket, UV Resistant, OD=Ø10.0mm, Black
- * Cable Length Tolerance: 01M±40mm
02M~05M:±60mm
06M~10M:±100mm
11M~30M:±200mm
31M~99M:±500mm

UNIT : mm

TOLERANCE

± 0.5 mm $\triangle B$

TITLE	Large Size, Lock Type MConn. 3MPin(20A)+5FPin(2A)
-------	--

SCALE 1 : 1	SIZE A4	SHEET 1 OF 1
REV. B	WC-REV. B.2	QC: Inspection item

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY	DATE
	Ruru	2013-08-20
DWG NO	CHECKED BY	DATE
DCU-08AMEM-LL7BXX	Rita	2013-08-20
CUSTOMER	APPROVED BY	DATE
ALTW	Maslow	2013-08-20

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[DCU-08AMEM-LL7B02](#) [DCU-08AMEM-LL7B05](#) [DCU-08AMEM-LL7B10](#) [DCU-08AMEM-LL7B01](#)