



- *  Important Dimension To Check.
- * Waterproof Rate: IP67
- * Connector: Nylon+GF, Black
- * Female Pin: Copper Alloy, Gold Plated
- * Nut: Nylon+GF, Black
- * O-Ring: EPDM, Black
- * Cable: UL2464 24#18C+Drain+AL/My,
PVC Jacket, UV Resistant, OD=8.0, Black
- * Cable Length Tolerance: 01M:±40mm
02M~05M:±60mm
06M~10M:±100mm
11M~30M:±200mm
31M~99M:±500mm

UNIT:mm			TITLE Screw Type Cable Assembly-180° 18Pin Female Connector Female Pin(5A)			Amphenol LTW 安費諾亮泰企業股份有限公司		ITEM NO		DRAWN BY Ruru		DATE 2013-07-31				
TOLERANCE .X ±0.25 .XX ±0.1 .XXX ±0.05 ANGLES ±1°			SCALE 1:1		SIZE A4			SHEET 1 OF 1		DWG NO DD-18AFFM-SL7AXX		CHECKED BY Rita		DATE 2013-07-31		
REV. C			WC-REV. B.2		(QC): Inspection item			CUSTOMER ALTW		APPROVED BY Maslow		DATE 2013-07-31				

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[1DD-18AFFM-SL7A01](#)