


DD-18AMFM-LL7AXX

```

XX : 01~99Meters
01 : 01Meter
02 : 02Meters
.
.
99 : 99Meters

```

Cable Length(L):01~99Meters



Pin Assignments

Front View

Black	黑	9	Blue/White	藍/白	18
Red	紅	8	Green/White	綠/白	17
Pink	粉紅	7	Orange/White	橙/白	16
Gray	灰	6	Red/White	紅/白	15
Yellow	黃	5	Brown/White	棕/白	14
Green	綠	4	Black/White	黑/白	13
White	白	3	Light Green	淺綠	12
Blue	藍	2	Purple	紫	11
Brown	棕	1	Orange	橙	10
Wire Color	Conn.		Wire Color	Conn.	
			Pin Out		

Note :

- *  Important Dimension To Check.
- * Waterproof Rate: IP67
- * Connector: Nylon+GF, Black.
- * Female Pin: Copper Alloy Gold Plated.
- * Cable: UL2464 24AWG*18C+Drain+Al/My
PVC Jacket UV Resistant, OD=8.0, Black.
- * Cable Length Tolerance: 01M:40mm
02M~05M:±60mm
06M~10M:±100mm
11M~30M:±200mm
31M~99M:±500mm

UNIT: mm

TOLERANCE

± 0.5 mm

TITLE		LARGE CABLE LOCK 18PIN M CONN F PIN	
SCALE	1:1	SIZE	A4
REV.	D	SHEET	1 OF 1
	WC-REV.	A.1	QC: Inspection item

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY	DATE
	Sam	2015-01-09
DWG NO	CHECKED BY	DATE
DD-18AMFM-LL7AXX	Vicky	2015-01-09
CUSTOMER	APPROVED BY	DATE
ALTW	Rita	2015-01-09

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[DD-18AMFM-LL7A10](#) [DD-18AMFM-LL7A02](#) [DD-18AMFM-LL7A01](#) [DD-18AMFM-LL7A05](#)