



REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN-0C0608~611	2010/11/26	Ivan	Change View
C	LEN1630215~218	2016/02/17	Ruru	Change Logo & Note



DD-18BMFM-LL6AXX

XX:01~99Meter
01:01Meter
02:02Meters
...
99:99Meters

Cable Length(L):01~99Meters



Pin Assignments
Front View 前視圖

Black	黑	9	Blue/White	藍/白	18
Red	紅	8	Green/White	綠/白	17
Pink	粉紅	7	Orange/White	橙/白	16
Gray	灰	6	Red/White	紅/白	15
Yellow	黃	5	Brown/White	棕/白	14
Green	綠	4	Black/White	黑/白	13
White	白	3	Light Green	淺綠	12
Blue	藍	2	Purple	紫	11
Brown	棕	1	Orange	橙	10
Wire Color	Conn.		Wire Color	Conn.	

Pin Out

△ Note:

- * △ Important Dimension.
- * Waterproof Rate: IP66
- * Housing: Nylon+GF, Black
- * Femal pin: Copper Alloy, Gold Plated
- * Cable:UL2464 24AWG*18C+D+AL/My PVC Jacket UV Resistant,OD=8.0mm, Black
- * Cable Length Tolerance:01M:±40mm
02M~05M:±60mm
06M~10M:±100mm
11M~30M:±200mm
31M~99M:±500mm

UNIT:mm		TITLE
TOLERANCE		LARGE CABLE LOCK 18PIN M CONN F PIN
±0.5 mm	SCALE Free	SHEET 1 OF 1
	REV. C	SIZE A4
		QC :Inspection Item

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY Ruru	DATE 2016/02/17
DWG NO DD-18BMFM-LL6AXX	CHECKED BY Rita	DATE 2016/02/17
CUSTOMER ALTW	APPROVED BY Lisa	DATE 2016/02/17

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[DD-18BMFM-LL6A01](#) [DD-18BMFM-LL6A02](#) [DD-18BMFM-LL6A05](#) [DD-18BMFM-LL6A10](#)