



REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LE3-710147	2006/12/13	Gao Ling	Move O-ring to ZSE00100842
C	LEN1350172	2013/05/08	Sam	Modify Dimension



Note:

* \varnothing Important Dimension.

* Waterproof Rate : IP68

IP68: 1M of depth of water 24 hours

(防水等級 : IP68)

(IP68: 1米水深 24 小時)

* Do Mating Test After Glued

點膠後，須作對插測試

* Add glue can't highly exceed pin

(點膠高度不得蓋過 pin 針)



* DVI Conn. : Nylon66, Black Core

* Plastic Jacket : Nylon+GF, Black


* Pin : Copper Alloy, Gold Plated

* Ring : Light Silicone, Blue

* Screw : Copper Alloy, Nickel Plated, #4-40 UNC

Screw L=5.0 For Panel Thickness
Under 1.2mm
適用板厚為 1.2mm 以下Screw L=6.0 For Panel Thickness
Between 1.2~2.0mm
適用板厚為 1.2~2.0mmRecommended Panel Cut-Out
建議挖孔尺寸

UNIT:mm

TOLERANCE
.X ±0.25
.XX ±0.1
.XXX ±0.05
ANGLES ±1°

TITLE

Female DVI Connector(18+5)

SCALE

1:1

SIZE

A4

SHEET

OF

1

REV.

C

WC-REV.

A.2

 \varnothing Inspection item

Amphenol LTW

安費諾亮泰企業股份有限公司

ITEM NO

DIS-23PFFS-SL8001

DWG NO

DIS-23PFFS-SL8001

CUSTOMER

ALTW

DRAWN BY

SamChang

CHECKED BY

Rita

APPROVED BY

Maslow

DATE

2013-05-08

DATE

2013-05-08

DATE

2013-05-08

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[DIS-23PFFS-SL8001](#)