


PRODUCT DATA DRAWING

| REVISION HISTORY | | | |
|------------------|-------------|------|----------|
| REV | DESCRIPTION | DATE | APPROVED |
| - | NRN42968 | 3/19 | GPF |
| | | | |



MATERIAL:

- CONNECTORS: 2 X 2.4MM PLUG (SF1611-60001)
- CABLE: FLEXIBLE Ø.047 CABLE
- SHRINK TUBING: M23053/5

PERFORMANCE:

- IMPEDANCE: 50 OHMS
- FREQ. RANGE: DC TO 50.0 GHz

| SV P/N | OAL |
|-----------|--------|
| 7016-0056 | 6.000 |
| 7016-0057 | 12.000 |

| | | | |
|---|--|---|--|
| MATERIAL: SEE NOTES | DIMENSIONS ARE IN INCHES TOLERANCES: FRACTIONAL: ±1/64 ANGULAR: X° ±1°0' X°X' ±15' DECIMAL: X ±.030 .XX ±.010 .XXX ±.005 INTERPRET DIMENSIONS AND TOLERANCES PER ASME Y14.5M - 1994 | UNLESS OTHERWISE SPECIFIED 1) ALL DIMENSIONS ARE IN INCHES (MILLIMETERS) 2) ALL DIMENSIONS ARE AFTER PLATING. 3) BREAK CORNERS & EDGES .005 R. MAX. 4) CHAM. 1ST & LAST THREADS. 5) SURFACE ROUGHNESS 63 MIL-STD-10. 6) DIA.'S ON COMMON CENTERS TO BE CONCENTRIC WITHIN .005 T.I.R. 7) REMOVE ALL BURRS | |
| FINISH: SEE NOTES | | | |
| SURFACE AREA: N/A | THIRD ANGLE PROJECTION | DRAWN: SJ 3/20/19 CHECKED: GPF 3/20/19 APPROVED: GPF 3/20/19 | TITLE: 2.4MM PLUG TO 2.4MM PLUG FOR FLEXIBLE Ø.047 CABLE ASSEMBLY |
| PROPRIETARY THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF SV MICROWAVE, INC. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF SV MICROWAVE, INC IS PROHIBITED. | | SIZE: B CAGE CODE: 95077 DWG. NO.: 7016-0056-0057 SCALE: 2:1 SHEET 1 OF 1 | |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[7016-0057](#)