


ROHS COMPLIANT		<div>PRODUCT DATA DRAWING</div>		REVISION HISTORY			
REV	DESCRIPTION			DATE	APPROVED		
-	NRN 45290			11/20	BNK		



MATERIAL:

CONNECTORS:

CABLE:

STRAIN RELIEF:

PERFORMANCE:

IMPEDANCE:

FREQ. RANGE:

2.92mm FEMALE IP68 (1521-60189)


2.92mm MALE (SF1511-60071)

T-FLEX 405 (200-70-139)

M23053/5

50 OHMS

DC TO 40.0 GHz.

MATERIAL:	SEE NOTES	DIMENSIONS ARE IN INCHES TOLERANCES: FRACTIONAL: ±1/64 ANGULAR: X° ±1°0' X°X' ±15' DECIMAL: .X ±.030 .XX ±.010 .XXX ±.005 INTERPRET DIMENSIONS AND TOLERANCES PER ASME Y14.5M - 1994	UNLESS OTHERWISE SPECIFIED 1) ALL DIMENSIONS ARE IN INCHES (MILLIMETERS) 2) ALL DIMENSIONS ARE AFTER PLATING. 3) BREAK CORNERS & EDGES .005 R. MAX. 4) CHAM. 1ST & LAST THREADS. 5) SURFACE ROUGHNESS 63-MIL-STD-10. 6) DIA.'S ON COMMON CENTERS TO BE CONCENTRIC WITHIN .005 T.I.R. 7) REMOVE ALL BURRS	<div>Amphenol SV MICROWAVE</div> <div>www.svmicrowave.com</div>		
FINISH:	SEE NOTES					
SURFACE AREA:	N/A					
PROPRIETARY <small>THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF SV MICROWAVE, INC. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF SV MICROWAVE, INC IS PROHIBITED.</small>		THIRD ANGLE PROJECTION	DRAWN: JPM 11/02/20		TITLE: 2.9MM STR. IP68 BLKHD F TO 2.9MM STR. M TFLEX 405 CABLE ASSEMBLY	
			CHECKED: BNK 11/02/20			SIZE DWG. NO. B 7015-1050
			APPROVED: BNK 11/02/20		SCALE: 4:1	SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[7015-1050](#)