


ROHS COMPLIANT

PRODUCT DATA DRAWING

REVISION HISTORY			
REV	DESCRIPTION	DATE	APPROVED
01	PRELIMINARY	03/14	STW
-	NRN 38806	05/14	STW




MATERIAL:

2 SMP R/A FEMALE CONNECTORS:	1214-4001
T-FLEX 405 CABLE:	200-70-139
SINGLE WALL TUBING:	M23053/5 (BLACK)

SV P/N	L (OAL)	INSERTION LOSS dB MAX.
7012-0799	6.000"	1.29
7012-0800	12.000"	1.96
7012-0801	24.000"	3.30

PERFORMANCE:

IMPEDANCE:	50 OHMS
FREQ. RANGE:	DC TO 26.5 GHz
VSWR:	1.85:1 DC TO 26.5 GHz
INSERTION LOSS:	SEE TABLE

MATERIAL:	SEE NOTES	DIMENSIONS ARE IN INCHES TOLERANCES:		UNLESS OTHERWISE SPECIFIED		SV Microwave, Inc. 2400 Centrepark West Drive, Suite 100 West Palm Beach, FL 33409	
FINISH:	SEE NOTES	FRACTIONAL: $\pm 1/64$ ANGULAR: $X^\circ \pm 1^\circ 0'$ $X^\circ X' \pm 15'$		1) ALL DIMENSIONS ARE IN INCHES (MILLIMETERS) 2) ALL DIMENSIONS ARE AFTER PLATING. 3) BREAK CORNERS & EDGES .005 R. MAX. 4) CHAM. 1ST & LAST THREADS. 5) SURFACE ROUGHNESS 63-MIL-STD-10. 6) DIA'S ON COMMON CENTERS TO BE CONCENTRIC WITHIN .005 T.I.R. 7) REMOVE ALL BURRS		TITLE: SMP R/A FEMALE TO SMP R/A FEMALE T-FLEX 405 CABLE ASSEMBLY	
SURFACE AREA:	N/A	DECIMAL: .X $\pm .030$ $.XX \pm .010$ $.XXX \pm .005$		INTERPRET DIMENSIONS AND TOLERANCES PER ASME Y14.5M - 1994		SIZE B CAGE CODE 95077 DWG. NO. 7012-0799-0801	
PROPRIETARY		THIRD ANGLE PROJECTION		DRAWN: BNK 03/27/14		SCALE: 6:1	
THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF SV MICROWAVE, INC. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF SV MICROWAVE, INC IS PROHIBITED.				CHECKED: STW 03/27/14		SHEET 1 OF 1	
				APPROVED: STW 03/27/14			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[7012-0800](#)