

ROHS COMPLIANT

PRODUCT DATA DRAWING

REVISION HISTORY			
REV	DESCRIPTION	DATE	APPROVED
-	DCN 46496	06/17	GPF

The drawing shows a cable assembly with a straight plug connector on the left and a straight jack connector on the right. The overall length is labeled 'OAL (SEE TABLE)'. The plug connector is labeled '1221-4009' and the jack connector is labeled 'SF1511-60071'. The cable is shown with a break in the middle, indicated by two parallel diagonal lines.

MATERIAL:

CONNECTORS:

CABLE:

SHRINK TUBING:

PERFORMANCE:

IMPEDANCE:

FREQ. RANGE:

SEE NOTES

2.92mm STRAIGHT PLUG (SF1511-60071)
SMP STRAIGHT JACK (1221-4009)



T-FLEX 405 (200-70-139)

M23053/5

50 OHMS

DC TO 40.0 GHZ

SV P/N	L (OAL)
7012-1283	6.000"
7012-1284	12.000"
7012-1285	24.000"

MATERIAL:	SEE NOTES	DIMENSIONS ARE IN INCHES TOLERANCES:	UNLESS OTHERWISE SPECIFIED 1) ALL DIMENSIONS ARE IN INCHES (MILLIMETERS) 2) ALL DIMENSIONS ARE AFTER PLATING. 3) BREAK CORNERS & EDGES .005 R. MAX. 4) CHAM. 1ST & LAST THREADS. 5) SURFACE ROUGHNESS 63 MIL-STD-10. 6) DIA.'S ON COMMON CENTERS TO BE CONCENTRIC WITHIN .005 T.I.R. 7) REMOVE ALL BURRS	<div><p>2400 Centrepark West Drive, Suite 100 West Palm Beach, FL 33409</p></div> <div>TITLE: SMP FEMALE TO 2.92mm MALE FOR .085 CABLE ASSEMBLY</div>	
FINISH:	SEE NOTES	FRACTIONAL: ±1/64 ANGULAR: X° ±1°0' X°X' ±15'			
SURFACE AREA:	N/A	DECIMAL: .X ±.030 .XX ±.010 .XXX ±.005			
THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF SV MICROWAVE, INC. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF SV MICROWAVE, INC IS PROHIBITED.					
THIRD ANGLE PROJECTION		DRAWN: VB 06/02/17	SIZE: B	CAGE CODE: 95077	DWG. NO.: 7012-1283-1284-1285
<div></div>		CHECKED: GPF 06/02/17	SCALE: 1:1		SHEET 1 OF 1
		APPROVED: GPF 06/02/17			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[7012-1285](#)