


ROHS COMPLIANT

PRODUCT DATA DRAWING

REVISION HISTORY			
REV	DESCRIPTION	DATE	APPROVED
-	NRN 42971	04/19	GPF



MATERIAL:

CONNECTORS: 2.4MM PLUG(SF1611-60003)
2.92MM PLUG(SF1511-60071)

CABLE: T-FLEX 405



SHRINK TUBING: M23053/5

PERFORMANCE:

IMPEDANCE: 50 OHMS

FREQ. RANGE: DC TO 40.0 GHz

SV P/N	OAL
7016-0062	6.000
7016-0063	12.000

MATERIAL:	SEE NOTES	<div>DIMENSIONS ARE IN INCHES TOLERANCES:</div> <div>FRACTIONAL: $\pm 1/64$ ANGULAR: $X^\circ \pm 1^\circ 0'$ $X^\circ X' \pm 15'$</div> <div>DECIMAL: $.X \pm .030$ $.XX \pm .010$ $.XXX \pm .005$</div> <div>INTERPRET DIMENSIONS AND TOLERANCES PER ASME Y14.5M - 1994</div>	<div>UNLESS OTHERWISE SPECIFIED</div> <div>1) ALL DIMENSIONS ARE IN INCHES (MILLIMETERS) 2) ALL DIMENSIONS ARE AFTER PLATING. 3) BREAK CORNERS & EDGES .005 R. MAX. 4) CHAM. 1ST & LAST THREADS. 5) SURFACE ROUGHNESS 63 - MIL-STD-10. 6) DIA. 'S ON COMMON CENTERS TO BE CONCENTRIC WITHIN .005 T.I.R. 7) REMOVE ALL BURRS</div>	<div> 2400 Centrepark West Drive, Suite 100 West Palm Beach, FL 33409</div>		
FINISH:	SEE NOTES			TITLE: 2.4MM PLUG TO 2.92MM PLUG FOR Ø.085 T-FLEX CABLE ASSEMBLY		
SURFACE AREA:	N/A			SIZE B	CAGE CODE 95077	DWG. NO. 7016-0062-0063
<div>PROPRIETARY</div> <div>THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF SV MICROWAVE, INC. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF SV MICROWAVE, INC IS PROHIBITED.</div>				SCALE: 2:1		
THIRD ANGLE PROJECTION		DRAWN: SJ 04/24/19		SHEET 1 OF 1		
		CHECKED: GPF 04/24/19				
		APPROVED: GPF 04/24/19				

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[7016-0063](#)