


ROHS COMPLIANT

# PRODUCT DATA DRAWING

REVISION HISTORY			
REV	DESCRIPTION	DATE	APPROVED
-	DCN 46701	08/17	GPF



**MATERIAL:**

CONNECTORS: SMA STRAIGHT FEMALE (2921-6002)  
SMPM STRAIGHT FEMALE (3221-40006)

CABLE: T-FLEX 405 (200-70-139)



SHRINK TUBING: M23053/5

## PERFORMANCE:

IMPEDANCE: 50 OHMS

FREQ. RANGE: DC TO 18.0 GHZ

SV P/N	L (OAL)
7029-2561	6.000"
7029-2562	12.000"
7029-2563	24.000"

MATERIAL:	SEE NOTES	DIMENSIONS ARE IN INCHES TOLERANCES:		UNLESS OTHERWISE SPECIFIED		 2400 Centrepark West Drive, Suite 100 West Palm Beach, FL 33409	
FINISH:	SEE NOTES	FRACTIONAL: $\pm 1/64$ ANGULAR: $X^\circ \pm 1^\circ 0'$ $X^\circ X' \pm 15'$		1) ALL DIMENSIONS ARE IN INCHES (MILLIMETERS) 2) ALL DIMENSIONS ARE AFTER PLATING. 3) BREAK CORNERS & EDGES .005 R. MAX. 4) CHAM. 1ST & LAST THREADS. 5) SURFACE ROUGHNESS 63 MIL-STD-10. 6) DIA.'S ON COMMON CENTERS TO BE CONCENTRIC WITHIN .005 T.I.R. 7) REMOVE ALL BURRS		TITLE: SMA FEMALE TO SMPM FEMALE FOR .085 CABLE ASSEMBLY	
SURFACE AREA:	N/A	DECIMAL: $X \pm .030$ $.XX \pm .010$ $.XXX \pm .005$					
<b>PROPRIETARY</b>  THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF SV MICROWAVE, INC. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF SV MICROWAVE, INC IS PROHIBITED.		INTERPRET DIMENSIONS AND TOLERANCES PER ASME Y14.5M - 1994				SIZE <b>B</b> CAGE CODE <b>95077</b> DWG. NO. <b>7029-2561-2563</b>  SCALE: 1:1 SHEET 1 OF 1	
		THIRD ANGLE PROJECTION		DRAWN: VB 08/04/17			
				CHECKED: GPF 08/04/17  APPROVED: GPF 08/04/17			

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[7029-2562](#)