


ROHS COMPLIANT

PRODUCT DATA DRAWING

REVISION HISTORY			
REV	DESCRIPTION	DATE	APPROVED
-	DCN 46701	08/17	GPF



MATERIAL:

CONNECTORS: SMA STRAIGHT FEMALE (2926-6015)
SMPM STRAIGHT FEMALE (3221-40007)

CABLE: STANDARD FLEXTRA CABLE (200-70-214)



SHRINK TUBING: M23053/5

PERFORMANCE:

IMPEDANCE: 50 OHMS

FREQ. RANGE: DC TO 18.0 GHZ

SV P/N	L (OAL)
7029-2558	6.000"
7029-2559	12.000"
7029-2560	24.000"

MATERIAL:	SEE NOTES		DIMENSIONS ARE IN INCHES TOLERANCES:		UNLESS OTHERWISE SPECIFIED		 2400 Centrepark West Drive, Suite 100 West Palm Beach, FL 33409	
FINISH:	SEE NOTES		FRACTIONAL: $\pm 1/64$ ANGULAR: $X^{\circ} \pm 1^{\circ} 0'$ $X^{\circ} X' \pm 15'$		1) ALL DIMENSIONS ARE IN INCHES (MILLIMETERS) 2) ALL DIMENSIONS ARE AFTER PLATING. 3) BREAK CORNERS & EDGES: .005 R. MAX. 4) CHAM. 1ST & LAST THREADS. 5) SURFACE ROUGHNESS 63 μ MIL-STD-10. 6) DIA.'S ON COMMON CENTERS TO BE CONCENTRIC WITHIN .005 T.I.R. 7) REMOVE ALL BURRS		TITLE: SMA FEMALE TO SMPM FEMALE FOR .047 CABLE ASSEMBLY	
SURFACE AREA:	N/A		DECIMAL: $.X \pm .030$ $.XX \pm .010$ $.XXX \pm .005$				SIZE: B CAGE CODE: 95077 DWG. NO. 7029-2558-2560	
PROPRIETARY			INTERPRET DIMENSIONS AND TOLERANCES PER ASME Y14.5M - 1994		DRAWN: VB 08/04/17		SCALE: 1:1	
THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF SV MICROWAVE, INC. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF SV MICROWAVE, INC IS PROHIBITED.	THIRD ANGLE PROJECTION				CHECKED: GPF 08/04/17		SHEET 1 OF 1	
					APPROVED: GPF 08/04/17			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[7029-2558](#)