


ROHS COMPLIANT

# PRODUCT DATA DRAWING

REVISION HISTORY			
REV	DESCRIPTION	DATE	APPROVED
-	DCN 46701	08/17	GPF



**MATERIAL:**

CONNECTORS: 2X SMA STRAIGHT MALE (SF2906-6002)

CABLE: T-FLEX 405 (200-70-139)



SHRINK TUBING: M23053/5

## PERFORMANCE:

IMPEDANCE: 50 OHMS

FREQ. RANGE: DC TO 18.0 GHZ

SV P/N	L (OAL)
7029-2552	6.000"
7029-2553	12.000"
7029-2554	24.000"

MATERIAL: SEE NOTES		DIMENSIONS ARE IN INCHES TOLERANCES:		UNLESS OTHERWISE SPECIFIED		<div> 2400 Centrepark West Drive, Suite 100 West Palm Beach, FL 33409</div>	
FINISH: SEE NOTES		FRACTIONAL: ±1/64    ANGULAR: X° ±1°0'    X°X' ±15'					
SURFACE AREA: N/A		DECIMAL: .X    ±.030 .XX    ±.010 .XXX ±.005		1) ALL DIMENSIONS ARE IN INCHES (MILLIMETERS) 2) ALL DIMENSIONS ARE AFTER PLATING. 3) BREAK CORNERS & EDGES: .005 R. MAX. 4) CHAM. 1ST & LAST THREADS. 5) SURFACE ROUGHNESS 63 MIL-STD-10. 6) DIA.'S ON COMMON CENTERS TO BE CONCENTRIC WITHIN .005 T.I.R. 7) REMOVE ALL BURRS		TITLE:  SMA MALE TO SMA MALE FOR .085 CABLE ASSEMBLY	
		INTERPRET DIMENSIONS AND TOLERANCES PER ASME Y14.5M - 1994					
PROPRIETARY		THIRD ANGLE PROJECTION		DRAWN: VB 08/04/17		SIZE B    CAGE CODE 95077    DWG. NO. 7029-2552-2554	
THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF SV MICROWAVE, INC. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF SV MICROWAVE, INC IS PROHIBITED.				CHECKED: GPF 08/04/17			
				APPROVED: GPF 08/04/17		SCALE: 1:1	
						SHEET 1 OF 1	

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[7029-2552](#)