


REV	DESCRIPTION	DATE	APPROVED
-	DCN 46496	06/17	GPF

PRODUCT DATA DRAWING

**MATERIAL:**

CONNECTORS: 2X SMPM STRAIGHT FEMALE (3221-40006)

CABLE: T-FLEX 405 (200-70-139)

SHRINK TUBING: M23053/5

PERFORMANCE:

IMPEDANCE: 50 OHMS

FREQ. RANGE: DC TO 40.0 GHz

MATERIAL: SEE NOTES

FINISH: SEE NOTES

SURFACE AREA: N/A

PROPRIETARY

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF SV MICROWAVE, INC. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF SV MICROWAVE, INC IS PROHIBITED.

DIMENSIONS ARE IN INCHES TOLERANCES:

FRACTIONAL: $\pm 1/64$ ANGULAR: $X^\circ \pm 1^\circ 0'$ $X^\circ X' \pm 15'$ DECIMAL: $.X \pm .030$ $.XX \pm .010$ $.XXX \pm .005$

INTERPRET DIMENSIONS AND TOLERANCES

PER ASME Y14.5M - 1994

UNLESS OTHERWISE SPECIFIED

1) ALL DIMENSIONS ARE IN INCHES (MILLIMETERS)

2) ALL DIMENSIONS ARE AFTER PLATING.

3) BREAK CORNERS & EDGES .005 R. MAX.

4) CHAM. 1ST & LAST THREADS.

5) SURFACE ROUGHNESS 63 μ MIL-STD-10.

6) DIA.'S ON COMMON CENTERS TO BE CONCENTRIC

WITHIN .005 T.I.R.

7) REMOVE ALL BURRS

THIRD ANGLE PROJECTION

DRAWN: VB 06/05/17

CHECKED: GPF 06/05/17

APPROVED: GPF 06/05/17

SV MICROWAVE
Amphenol
2400 Centrepark West Drive, Suite 100
West Palm Beach, FL 33409

TITLE: SMPM FEMALE TO SMPM
FEMALE FOR .085 CABLE
ASSEMBLY

SIZE CAGE CODE DWG. NO.
B 95077 7032-7153-7154-7155
SCALE: 1:1 SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[7032-7154](#)