







SIGN	DATE	DESCRIPTION	APPROVER
△			
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material:

- Item ① Terminal housing: PBT (UL94V-0)
- Item ② Male contact : Copper. Gold plated.
- Item ③ With flange nut: Steel zinc plated.

Electrical:

- Voltage rating: 600 V
- Current rating: 115 A
- Withstanding Voltage: 2.2 KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 250°C±10°C/5 Sec

KU xx C 0 x 1 xxxx G

No. OF POLES
02: 2 POLES
:
10: 10 POLES

COLOR

- 0: BLACK
- 5: GREEN (RAL 6018/T)
- 6: BLUE
- 8: GREY (RAL 7035/D)

G: Pb<40000ppm
0000: "@" Logo (Standard)
000A: "ANYTEK" Mark
Any special item by customer request.
please contact sales department.

POLE		2	3	4	5	6	7	8	9	10
Dim.L		31.4	46.4	61.4	76.4	91.4	106.4	121.4	136.4	151.4
Dim.P		15.0	30.0	45.0	60.0	75.0	90.0	105.0	120.0	135.0
Tol.		±0.20			±0.35			±0.50		

ANYTEK				CUSTOMER COPY			
				ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD			
TITLE	KU 15.0mm Body Series (Right angle) without flange 2P-10P						
PART NO.	KUxxC0x1xxxxG			DWG NO.	8KU0005		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			Tolerance
		Runner 2011.04.25	Runner 2010.05.24			UNIT: mm	X. ±0.50
						SCALE: NONE	X.X ±0.30
				SHFFT: 01/01		RFV: B	X.XX ±0.10
							X° ±1°

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[KU02C0510000G](#) [KU03C0510000G](#) [KU04C0510000G](#) [KU05C0510000G](#) [KU06C0510000G](#) [KU07C0510000G](#)
[KU08C0510000G](#) [KU09C0510000G](#) [KU10C0510000G](#)