


SIGN	DATE	DESCRIPTION	APPROVER
△			
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			





Material

- Item a Male contact pin:Brass (CuZn)
- Item b Terminal(housing): Thermoplastic (UL94V-0)

Electrical cULus

- Voltage rating: 300V
- Current rating: 10A
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 250°C±10°C/5 Sec



OP xx 6 3 x x xxxx G

POLES

02,,pole,,


12 pole

G: Pb<4000ppm

0000: Standard
Any special item by
customer request.
please contact sales
department.

0 PA 66
1 PA46

- 0 Tin plated 200u"
- 1 Gold plateing 10u"
- 2 Gold flash



P.C.B LAYOUT

DIMENSION

A	N×8.0
B	(N-1)×8.0

N= NUMBER OF CONCATS

Poles	Tolerance
2P-6P	±0.15
7P-12P	±0.20
13P-18P	±0.30
19P-24P	±0.40

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		OP-8.0mm series			
PART NO.		OPxx63xxxxxxG		DWG NO.	80P0301
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	
	Marvin 2006.06.26	Marvin 2006.06.26	Marvin 2006.06.26	Tolerance	
				UNIT: mm	X. ±0.50
				SCALE: NONE	X.X ±0.30
				SHEET: 01/01	X.XX ±0.10
				REV.: C	X° ±1°

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

[OP0263000000G](#) [OP0363000000G](#) [OP0463000000G](#) [OP0563000000G](#) [OP0663000000G](#) [OP0763000000G](#)
[OP0863000000G](#) [OP0963000000G](#) [OP1063000000G](#) [OP1163000000G](#) [OP1263000000G](#) [OP1363000000G](#)
[OP1463000000G](#) [OP1563000000G](#) [OP1663000000G](#) [OP1763000000G](#) [OP1863000000G](#) [OP1963000000G](#)
[OP2063000000G](#)