


PRODUCT DATA DRAWING



MATERIAL

CONNECTORS: 2.92mm Bulkhead Female (SF1521-60045)
SMP Female QB (1221-40051)

CABLE: Ø.047 Flexible Coax

SHRINK TUBING: M23053/5

PERFORMANCE

IMPEDANCE: 50 Ohms

FREQ. RANGE: DC to 40 GHz

VSWR: 1.4:1 Max, DC to 18.0 GHz
1.6:1 Max, 18.0 + GHz

INSERTION LOSS: 1.89 dB Max

NOTES

1. See individual data drawings for connector specifications
2. Dimensions shown are in inches



TITLE:

2.92mm Bulkhead Female to SMP Female QB 6"
Cable Assembly for Ø.047 Flexible Coax

DWG. NO.

FB292-047-FQSMP-060

DRAWN

2022-10-14 13:53:56

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[FB292-047-FQSMP-060](#)