




Copyright FCI.



Knurle area compatible with housing
diameter : 4.80 to 4.85 mm

Notes :

Material : Brass
Plating : Gold over Nickel on entire part
Press-fit retention on board : 75N mini
(Board thickness > 2.4mm)

Press-fit hole : 3.02 to 3.20mm after reflow
(drilled diameter 3.20 to 3.26mm)




3-ROHS INFORMATIONS:

-This product meets European Union Directives and other
country regulations as described in GS-22-008.
-Termination plating 0.5 to 4µ Nickel + Gold on entire part
-Packaging spec: see GS-14-920.

FCI P/N 10062610-001LF

REV F - 2006-04-17

rev	ecn no	dr	date
A	LS06-0058	MLE	2006/03/13
B	LS06-0084	LGO	2006/06/20
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-

www.fciconnect.com			surface ISO 1302		- ✓	tolerance std ISO 406 ISO 1101		projection 		mm 		
TOLERANCES UNLESS OTHERWISE SPECIFIED												
Dr	MLenoir	2006/03/09	ANGULAR	LINEAR	0.X		±0.3		size	Scale		
Eng	MLenoir	2006/03/09			0.XX		±0.1		A3	10:1		
Chr	phLegare	2006/03/09			0° ±2°		0.XXX ±0.05					
Appr	PhLegare	2006/03/09	Product family						ECN LS06-0084			
			-						Spec ref			
			title				dwg no				Rev	
			MALE POWER CONTACT				10062610C				B	
			ACTIVE AREA LENGTH 8MM									
			catalog no				Y				sheet 1 of 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI / Amphenol:](#)

[10062610-001LF](#)