




PRODUCT NUMBER
89950-0XXLF

LEAD FREE, RoHS COMPLIANT
SEE NOTE 4




| STYLE | NBR OF POS | OMIT TERMINAL |
|-------|------------|---------------|
| 06 | 2x22 | 20 |

NOTES :

- 1 - MATERIAL :
TERMINAL PHOSPHORE BRONZE
BASE AND COVER : PBT GLASSFILLED UL 94V-0 BLACK
- 2 - PLATING :
GOLD $0.76\mu\text{m}$ Au MIN ON CONTACT AREA
NICKEL $1.27\mu\text{m}$ MIN UNDERPLATING ALL OVER
- 3 - RECOMMENDED CABLE SIZE : AWG28, STRANDED
- 4 - THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER
COUNTRY REGULATIONS AS PER GS-22-008.
PACKAGING SPECIFICATION AS PER GS-14-920.
- 5 - STRAIN RELIEF (OPTIONAL) P/N 10073978-044LF



VIEW WITHOUT COVER



| | | | | | | | | | | |
|-------------------------|----------------|-----|----------|---------------------------------------|-------------------------------|------------|--------------------------------------|--|--|--|
| mat'l. code SEE NOTE | | | | surface ISO 1302 | tolerance ISO 406 ISO 1101 | projection | product family MINITEK | | | |
| Ltr | ecn na | dr | date | tolerances unless otherwise specified | | mm | title POL 2.00mm IDC 0.76μm Au | | | |
| E | F08-0211 | LMU | 06.07.03 | angles | Linear | | scale 1:1 | | | |
| F | F07-0215 | LMU | 07.06.12 | 0'±x' | | | | | | |
| | | | | dr | LMULIN | 07.06.12 | FCJ | | | |
| | | | | engr | J.COMPAIGNON | 07.06.12 | | | | |
| | | | | chr | | | | | | |
| | | | | appd | JM.C | 07.06.12 | type Product Customer Drawing | | | |
| sheet index | revision sheet | | | | | | | | | |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI / Amphenol:](#)

[89950-006LF](#)