




DIMENSIONS




P.C. CARD DRILLING (Component side view)

See drawing ref. C-8609-0000



rev	ecn no	dr	date
B	-	ROU	2002/03/27
C	LS05-001	JTA	2005/03/04
D	LS06-0095	LGO	2006/06/28
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-

TERMINATION



TIN LEAD PART NUMBER

PART NUMBER

86093967113755881E1

LEAD FREE PART NUMBER

PART NUMBER

86093967113755CBLF

SPECIFICATION 881 = 7 standard pins in cavities a1-b1-c1-a32-b32-c31-c32
OR SPECIFICATION CB = short pins in other positions

GENERAL CHARACTERISTICS AND ROHS INFORMATIONS: SEE DRAWING C-8609-0000A

European Views

www.fciconnect.com			surface ISO 1302		tolerance std ISO 406 ISO 1101		projection 		mm 	
			TOLERANCES UNLESS OTHERWISE SPECIFIED							
Dr	ROUILLARD	2002/03/15	ANGULAR	LINEAR	0.X	±0.1	size A3	Scale 1.5		
Eng	TARON	2002/03/15			0.XX	±0.1		ECN LS06-0095		
Chr	LEGARE	2002/03/15			0.XX' ±2"	0.XXX			±0.1	
Appr	LEGARE	2002/03/15	Product family DIN 8609				Spec ref -			
			title STANDARD MALE 3 ROW 96 CONTACTS				dwg no C-8609-1127			Rev D
catalog no			-				CUSTOMER			sheet 1 of 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI / Amphenol:](#)

[86093967113755CBLF](#)