

TIN LEAD PART NUMBER

SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	PART NUMBER
09	30.81	24.99	16.96	16.21	10.96	D09S24B.PV00
15	39.14	33.32	25.18	24.54	19.18	D15S24B.PV00
25	53.03	47.04	39.12	38.25	33.12	D25S24B.PV00
37	69.32	63.50	55.68	54.71	49.68	D37S24B.PV00


Protection:	4 --> flash AU
	6 --> 0.76 μ AU

LEAD FREE PART NUMBER

SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	PART NUMBER
09	30.81	24.99	16.96	16.21	10.96	D09S24B.PV00LF
15	39.14	33.32	25.18	24.54	19.18	D15S24B.PV00LF
25	53.03	47.04	39.12	38.25	33.12	D25S24B.PV00LF
37	69.32	63.50	55.68	54.71	49.68	D37S24B.PV00LF





Protection: 4 --> flash AU
6 --> 0.76μ AU

PC card drilling dimensions(after plating)
(thickness 2.40±0.20mm)



rev	ecn no	dr	date
B	-	-	1996/09/05
C	LS05-001	MPE	2005/03/10
D	LS05-0056	MPE	2005/06/27
E	LS06-0097	LGO	2006/07/29
-	-	-	-
-	-	-	-
-	-	-	-

GENERAL CHARACTERISTICS AND ROHS INFORMATION:
SEE DRAWING C01-8646-0000

www.fciconnect.com			surface ISO 1302 		tolerance std ISO 406 ISO 1101		projection 		 mm	
			TOLERANCES UNLESS OTHERWISE SPECIFIED							
Dr	LELEON	1992/09/16	ANGULAR	LINEAR	0.X	±0.1	size A3	Scale 2		
Eng	PESSON	1992/09/16			0.XX	±0.1				
Chr	LEGARE	1992/09/16			0.XXX	±0.1		ECN LS06-0097		
Appr	LEGARE	1992/09/16	Product family				D-SUB	Spec ref -		
			FEMALE CONNECTOR STD EURO straight solder type for				dwg no C01-8646-0123		Rev. E	
			catalog no				-		CUSTOMER	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[D09S24B4PV00LF](#) [D25S24B4PV00LF](#) [D09S24B6PV00LF](#) [D15S24B6PV00LF](#)