






PRODUCT NUMBER	PLATING	PACKAGING TYPE
10098870-1102LF	0.76μm Au	TAPE & REEL WITH MYLAR



www.fciconnect.com			surface ASME Y14.5	tolerance std ASME Y14.5	projection	MM
			TOLERANCES UNLESS OTHERWISE SPECIFIED			
Dr	S.MANOCHARAN	2009-03-30	ANGULAR	LINEAR	0.X	±0.25
Eng	J.SHUEY	2009-03-30			0.XX	±0.13
Chr	J.SHUEY	2009-03-30	0°	±1°	0.XXX	±-
Appr	J.SHUEY	2009-03-30	Product family		MINI SAS	ECN V09-0420
			Spec ref		-	

rev	ecn no	dr	date	R/A SMT 0.80mm PITCH		dwg no	10098870	Rev.	C
A	V09-0420	RE	2009-08-20	MINI-SAS CONNECTOR					
B	V09-0508	MRG	2009-10-29						
C	V09-0550	MRG	2009-11-19						
-	-	-	-						
-	-	-	-						
-	-	-	-						
-	-	-	-						

PRODUCT NUMBER
10098870-1102LF



0.35±0.03 TYP
⊕ ∅ 0.05 (S) A B

1.80±0.03 TYP
⊕ ∅ 0.05 (S) A B

B

16.80

P.C.B. EDGE

5.00

4.60

B1

A1

5.00

4.60

0.80

0.40

FULL RADIUS

∅ 1.55±0.04

2.51

5.18

A

12.00±0.05

NOTES:

- CONTACT MATERIAL: COPPER ALLOY
PLATING:
UNDERPLATING: NICKEL PLATING OVER ALL THICKNESS 1.27µm MIN.
CONTACT AREA: GOLD PLATING (SEE TABLE)
HOUSING MATERIAL: HIGH-TEMP THERMOPLASTIC, COLOR: BLACK
FLAME RETARDANT PER UL 94V-0
- PRODUCT SPECIFICATION: GS-12-548
- APPLICATION SPECIFICATION: GS-20-124
- DATE CODE PRINTED APPROXIMATELY AS SHOWN.
- PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
- A SYMBOL WILL BE NEXT TO ANY DIMENSION, VIEW, OR NOTE WHICH HAS BEEN MODIFIED WITH THE CURRENT DRAWING REVISION.



R/A SMT 0.80mm PITCH
MINI-SAS CONNECTOR
catalog no

dwg no

10098870

Rev.
C

CUSTOMER

sheet 2 of 2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[10098870-1102LF](#)