




FCIconnect.com

Copyright FCI

PRODUCT NO.
74814-001
74814-001LF



WAS SK-39558

mat'l. code NOTE 1				surface ISO 1302	tolerance ISO 406 ISO 1101	projection INCH	product family MICROPAX
ltr	ecn	no	dr	date	tolerances unless otherwise specified		title
A	V80453	RGD	3/30/98		angles linear .XX±.01/0.3		MICROPAX 240P RECEPT.
B	V80815	SAR	5/18/98		.XXX±.005/0.13		STRADDLE LONG TAIL
C	M06-0363	MHT	9/18/06	0'±2'	.XXXX±.0020/0.051	scale 1.5:1	dwg no
				dr	RGD	2/9/98	sheet 1 of 3 size
				enr	D.JOHNESCU	2/9/98	74814
				chr	D.JOHNESCU	2/9/98	A3
				app	D.JOHNESCU	2/9/98	type
sheet	revision	C	C	C			Product Customer Drawing
index	sheet	1	2	3			


form: A3

PDM: Rev:C

STATUS Released

Printed: Jul 22, 2010

PRODUCT NO.	GUIDE PIN/STANDOFF
74814-002	YES GUIDE PIN
74814-003	NO
74814-002LF	YES GUIDE PIN
74814-003LF	NO



NOTES:

① MATERIALS:

DIELECTRIC: LCP
CONTACTS: PHOS. BRZ.
FRAME: ZINC ALLOY #3

② PLATING:

SOLDER TAILS: 150u"/3.81um Sn Pb
FRAME: 150u"/3.81um Sn
CONTACT:
30u"/.76um GXT OVER 50u"/1.27um Ni

LEAD FREE OPTION:

SOLDER TAILS: 100u"/2.54um Sn
FRAME: 150u"/3.81um Sn
CONTACT:
30u"/.76um GXT OVER 50u"/1.27um Ni

③ DO NOT REMOVE PROCESSING CAP UNTIL SOLDERING IS COMPLETED.

④ PART NUMBERS WITH LF SUFFIX AT THE END ARE LEAD FREE.

8 THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 20 SECONDS IN A CONVECTION, INFRA-RED OR VAPOR PHASE REFLOW OVEN.

⑨ IF "LF" P/N THE PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATION AS DECREIBED IN GS-22-008.

74814-002 SHOWN
SAME AS 74814-001 EXCEPT AS SHOWN

WAS SK-39558


mat'l. code				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection INCH	product family MICROPAX
ltr	ecr	no	dr	date	tolerances unless otherwise specified		title
C					angles linear .XX±.01/0.3 .XXX±.005/0.13 .XXXX±.0020/0.051	scale 1.5:1	MICROPAX 240P RECEPT. STRADDLE LONG TAIL
					dr RGD 2/9/98		dwg no sheet 2 of 3 size
					enr D.JOHNESCU 2/9/98		74814 A3
					chr D.JOHNESCU 2/9/98		type Product Customer Drawing
					appd D.JOHNESCU 2/9/98		
sheet index	revision sheet						



FCIconnect.com

Copyright FCI

PRODUCT NO.
SEE CHART



mat'l. code				surface	tolerance	projection	product family
				ISO 1302 ✓	ISO 406 ISO 1101	INCH	MICROPAX
ltr	ecn	no	dr	date	tolerances unless otherwise specified		title
C					angles	linear	MICROPAX 240P RECEPT.
					0°±2'		STRADDLE LONG TAIL
					dr	RGD	2/9/98
					enrg	D.JOHNESCU	2/9/98
					chr	D.JOHNESCU	2/9/98
					appd	D.JOHNESCU	2/9/98
sheet	revision						type
index	sheet						Product Customer Drawing

form: A3

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI / Amphenol:](#)

[74814-001](#)