


DIMENSIONS



TIN LEAD PART NUMBER

PART NUMBER


86094647113755121E1

LEAD FREE PART NUMBER

PART NUMBER

86094647113755AGLF

TERMINATION




SPECIFICATION 121 or AGLF = Grounding pins in position : A1 / A32
C1 / C32

GENERAL CHARACTERISTICS AND ROHS INFORMATION:

SEE DRAWING C-8609-0000A

PCB DRILLING

component side



rev	ecn no	dr	date
A	-	-	1997/11/25
B	LS07-0073	HLE	2007/03/07
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-

www.fciconnect.com			surface ISO 1302	tolerance std ISO 406 ISO 1101	projection mm
			TOLERANCES UNLESS OTHERWISE SPECIFIED		
Dr	ROUILLARD	1997/11/25	ANGULAR	0.X	±0.1
Eng	ROUILLARD	1997/11/25	LINEAR	0.XX	±0.1
Chr	P.LEGARE	1997/11/25		0.XXX	±0.1
Appr	P.LEGARE	1997/11/25	Product family	DIN STD	ECN LS07-0073
			Spec ref -		
			European Views		
			mm		
			A3		
			Scale 1.5		
			Rev. B		



STANDARD MALE 3 ROW
64 CONTACTS

dwg no C-8609-0676

See table CUSTOMER sheet 1 of 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI / Amphenol:](#)
[86094647113755AGLF](#)